

# METAL CLAD CABLE in a SIMpull BARREL™ CABLE DRUM

## WE LISTENED:

Reels are heavy and difficult to handle on the jobsite. This limits productivity, consumes valuable floor space and storage, and increases safety concerns.

## SOLUTION:

MC Cable in a SIMpull BARREL™ Cable Drum requires a fraction of the set-up time and effort compared to a wire cart and reels. Using barrels reduces physical effort required to pull wire, increasing safety and productivity. The SIMpull BARREL™ Cable Drums are available in a variety of MC constructions.

## FEATURES //

- Available in #14, 12, and 10 (up to 4 conductors for the largest size)
- Available in Aluminum and Steel Armor
- Available in MC<sup>AP</sup>® Metal Clad All Purpose Cable, HCF MC<sup>AP</sup>® Metal Clad All Purpose Cable, MC-PCS Duo™ Cable, and HCF MC-PCS Duo™ Cable
- Available in Custom Color configurations
- Available in Solid and Stranded constructions

## BENEFITS //

- Convenient cable drum package holds longer lengths
- Overall system increases productivity for branch circuit installations
- Less material handling and reduced wire remnants
- Designed to help reduce potential lifting/handling/pulling injuries
- No broken reels, flanges, or arbor holes



### ACCESSORIES

SIMpull BARREL™ Hand Truck SBT01

SIMpull BARREL™ Tripod SBT02

The Power of Connections™

Connect With Us | #SOUTHWIRE



**Southwire®**

©2017 - 2018 Southwire Company, LLC. All Rights Reserved.  
®Registered Trademark and ™ Trademark of Southwire Company, LLC.

**ARMORLITE® TYPE MC SIMpull BARREL™ CABLE DRUM**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
14-3C DRUM	Bk/We/Rd	68582611		0.464
12-2c DRUM	Bk/We	68580012	2500	0.475
12-2c DRUM	Rd/We		2500	0.475
12-2c DRUM	Be/We	68948912	2500	0.475
12-3c DRUM	Bk/We/Rd		2000	0.505
12-2c x 12-2c NPP DRUM	Bk/Rd/We-Bk/We-Rd	55279511	1500	0.539
10-2c DRUM	Bk/We		1500	0.542
10-2c DRUM	Rd/We	61052111	1500	0.542
10-2c DRUM	Be/We		1500	0.542
10-3c DRUM	Bk/We/Rd	68584211	1000	0.58
10-4c DRUM	Bk/We/Rd/Be		1000	0.623

**STRANDED CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c STR DRU	Bk/We	69114711	2000	0.494
12-2c STR DRUM	Rd/We	55231811	2000	0.494
12-2c STR DRUM	Be/We	55125611	2000	0.494
12-3c STR DRUM	Bk/We/Rd	69115411	1500	0.537
12-4c STR DRUM	Bk/We/Rd/Be	69116211	1000	0.564
10-2c STR DRUM	Bk/We	69117003	1000	0.566
10-2c STR DRUM	Rd/We	55127204	1000	0.566
10-2c STR DRUM	Be/We	55127004	1000	0.566
10-3c STR DRUM	Bk/We/Rd	69118803	1000	0.607
10-4c STR DRUM	Bk/We/Rd/Be	69119604	1000	0.607

**ARMORLITE® TYPE MC SIMpull BARREL™ CABLE DRUM 277V COLORS**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c DRUM	Bn/Gy	68936404	2500	0.475
12-3c DRUM	Bn/Oe/Gy	68956212	2000	0.505
12-4c DRUM	Bn/Oe/Yw/Gy	68957011	1500	0.539
10-2c DRUM	Bn/Gy	68960411	1500	0.542
10-3c DRUM	Bn/Yw/Gy	61055003	1000	0.58
10-4c DRUM	Bn/Oe/Yw/Gy	68941412	1000	0.623

**STRANDED CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c STR DRUM	Bn/Gy	55111006	2000	0.494
12-3c STR DRUM	Bn/Oe/Gy	55111405	1500	0.537
12-4c STR DRUM	Bn/Oe/Yw/Gy	55112205	1000	0.564
10-2c STR DRUM	Bn/Gy	55127612	1000	0.566
10-3c STR DRUM	Bn/Oe/Gy	55112105	1000	0.607

**MC-PCS DUO™ SIMpull BARREL™ CABLE DRUM**

**SOLID CONDUCTORS**

Size	Description	Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
Power		Control/Signal				
12-2c PCS	Bk/We	16-2c	Pe/Gy	59224003	1000'	0.58
12-2c PCS	Bn/Gy	16-2c	Pe/Gy	59224504	1000'	0.58
12-2c PCS	Rd/We	16-2c	Pe/Gy	64328203	1000'	0.663

**STRANDED CONDUCTORS**

Size	Description	Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
Power		Control/Signal				
12-2c STR PCS	Bk/We	16-2c	Pe/Gy	59224003	1000'	0.59
12-2c STR PCS	Bn/Gy	16-2c	Pe/Gy	59226103	1000'	0.59

**\* OTHER CONSTRUCTIONS AVAILABLE UPON REQUEST**

**MCAP® METAL CLAD ALL PURPOSE CABLE IN A SIMpull BARREL™ CABLE DRUM**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
14-2c MCAP DRUM	Bk/We (2x1500')	55527204	3000	0.392
12-2c MCAP DRUM	Bk/We	55510312	2500	0.43
12-3c MCAP DRUM	Bk/We/Rd	55510412	2000	0.447
12-4c MCAP DRUM	Bk/We/Rd/Be	55510504	1500	0.48
10-2c MCAP DRUM	Bk/We	55527504	1500	0.485
10-3c MCAP DRUM	Bk/We/Rd	55527712	1000	0.52
10-3c MCAP DRUM	Bk/Rd/Be	58902801	1000	0.52
10-4c MCAP DRUM	Bk/We/Rd/Be	55527804	1000	0.565

**STRANDED CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c STR MCAP DRUM	Bk/We	55637704	2500	0.437
12-3c STR MCAP DRUM	Bk/We/Rd	55645704	2500	0.468
12-4c STR MCAP DRUM	Bk/We/Rd/Be	55587404	1500	0.5
10-2c STR MCAP DRUM	Bk/We	55738703	1500	0.52

**MCAP® METAL CLAD ALL PURPOSE SIMpull BARREL™ CABLE DRUM 277V COLORS**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c MCAP DRUM	Bn/Gy	55572612	2500	0.43
12-3c MCAP DRUM	Bn/Oe/Gy	55572812	2000	0.447
12-4c MCAP DRUM	Bn/Oe/Yw/Gy	55573112	1500	0.48
10-2c MCAP DRUM	Bn/Gy	55573304	1500	0.485
10-3c MCAP DRUM	Bn/Yw/Pe	59943201	1000	0.522
10-4c MCAP DRUM	Bn/Yw/Pe/Gy	59936703	1000	0.565

**HCF MCAP® METAL CLAD ALL PURPOSE SIMpull BARREL™ CABLE DRUM**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c HCF DRUM	Bk/We	55527911	2500	0.45
12-3c HCF DRUM	Bk/We/Rd	55528011	1500	0.48
12-4c HCF DRUM	Bk/We/Rd/Be	55528111	1500	0.515

**STRANDED CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c STR HCF DRUM	Bk/We	55636104	2000	0.468
12-3c STR HCF DRUM	Bk/We/Rd	55636303	1500	0.51

**HCF MCAP® METAL CLAD ALL PURPOSE SIMpull BARREL™ CABLE DRUM BARRELS 277V COLORS**

**SOLID CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c HCF DRUM	Bn/Gy	55573911	2500	0.45
12-3c HCF DRUM	Bn/Oe/Yw	55574111	1500	0.48
12-4c HCF DRUM	Bn/Oe/Yw/Gy	55574303	1500	0.515

**STRANDED CONDUCTORS**

Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
12-2c STR HCF DRUM	Bn/Gy	55872403	2000	0.468

**MC-PCS HCF DUO™ SIMpull BARREL™ CABLE DRUM**

**SOLID CONDUCTORS**

Size	Description	Size	Description	Southwire Stock #	Package Quantity	OD (Inches)
Power		Control/Signal				
12-2c PCS HCF	Bk/We	16-2c	Pe/Gy	See MC Team	1000'	0.58
12-2c PCS HCF	Bn/Gy	16-2c	Pe/Gy	59812903	1000'	0.58



DOWNLOAD CONFIGURATOR APP AT:  
[www.southwire.com/apps](http://www.southwire.com/apps) iPad® only



Connect With Us | #SOUTHWIRE