

Flexible Metal Conduit. Crush/Corrosion Resistant.
Smooth Interior For Easy Pulling.



APPLICATIONS

Data-Flex® Flexible Metal Conduit is suitable for the following installations:

- Suitable for concealed, exposed, or approved raceways
- Can be used where listed products are not required

CONSTRUCTION

Data-Flex® is manufactured with a spiral wound strip of corrosion-resistant, hot-dipped galvanized steel with a heavy zinc coating.

FEATURES

- Smooth metal interior for easy wiring pulling
- Hot-dipped, heavy zinc coating for rust/corrosion resistance
- Superior crush-proof qualities

™Data-Flex is a trademark of Southwire Company

Data-Flex

Trade Size (Inches)	Approximate Weight (lbs/100 ft)	Outside Diameter (inches)	Approx. Bend Radius* (Inches)	Standard Coil Length (feet)	Standard Reel Length (feet)
3/8	12	.585	4	100/250	1000
1/2	19.5	.875	4	100	1000
3/4	23.5	1.075	5	100	1000
1	30	1.340	6	50	400
1-1/4	37	1.590	8	50	250
1-1/2	66	1.900	10	25	150
2	93	2.400	12	25	100
2-1/2	150	2.960	15	25	-
3	190	3.460	18	25	-
3-1/2	220	3.960	21	25	-
4	264	4.460	24	25	-

* Minimum bend radius based on NEC Chapter 9, Table 2 (other bends).