

HSJO/SJOOW

HPN/HSJO/SJOOW



APPLICATIONS Suitable for use as follows:

- Power supply to outdoor equipment, barbecues, portable power tools, lawn mowers, etc., where the cord is subjected to hard usage in dry or damp locations.

STANDARDS & REFERENCES

- Bare copper conductors
- CSA Spec. C22.2, No. 49; File listing LL224650
- UL Spec. No. 62; E46194

CONSTRUCTION

- Extra flexible HSJO bare or tinned copper conductors
- EPDM Insulation
- Twisted with paper fillers or available without fillers
- Overall oil resistant CPE jacket
- Available in dark colors only
- Flexible SJOOW

WEIGHTS, MEASUREMENTS AND PACKAGING

SIZE AWG	NO. OF COND.	NO. OF STRANDS	INSULATION THICKNESS		JACKET THICKNESS		OVERALL DIAMETER		AMPS	NET WEIGHT	
			mm	inches	mm	inches	mm	inches		kg/km	lbs/Mft
18	2	16	0.76	0.030	0.76	0.030	7.24	0.285	10	73	49
18	3	16	0.76	0.030	0.76	0.030	7.75	0.305	10	82	55
16	2	26	0.76	0.030	0.76	0.030	7.87	0.310	13	85	57
16	3	26	0.76	0.030	0.76	0.030	8.38	0.330	13	102	68
14	2	41	0.76	0.030	0.76	0.030	8.64	0.340	18	113	76
14	3	41	0.76	0.030	0.76	0.030	9.27	0.365	18	131	88
12	2	65	0.76	0.030	1.14	0.045	10.67	0.420	25	175	117
12	3	65	0.76	0.030	1.14	0.045	11.00	0.433	25	204	137
12	4	65	0.76	0.030	1.14	0.045	11.89	0.468	20	243	163

Bare Copper Conductors

90°C, 300 Volts



green Spec[™]
RoHS Compliant



Southwire[®]
OEM Division