SIM*pull*™ REEL
COMPARISON CHART







	Southwire™ SIM*pull*™ REEL	Wood Flange w/Steel Shaft	Steel Flange w/Wooden Reel	Steel Compartment Reel
Advantages:				
Chocks included to increase safety	✓	✓	✓	⊘
Parallels	✓	✓	✓	⊘
Pulling head compatible	✓	✓	✓	✓
Ability to cradle	✓	✓	✓	✓
Internal bearings to reduce drag	✓	⊘	⊘	⊘
Payoff tension adjustment	✓	⊘	⊘	⊘
Fits through 36'' wide doorways	✓	✓	⊘	⊘
Dual flange/axle bearings for easier mobility	✓	⊘	⊘	⊘
Will not damage finished floors*	✓	⊘	⊘	⊘
Does not require additional delivery steps	✓	✓	⊘	⊘
Does not require additional loading equipment	✓	✓	⊘	⊘
Does not require additional loading steps	✓	⊘	⊘	⊘
Does not need greasing to increase performance	✓	✓	⊘	✓
Does not need assembly parts/pieces	✓	✓	⊘	⊘
Does not require the use of a wooden reel	✓	⊘	⊘	✓
Specs:				
Flange diameter	61″	Up to 48″	50″	45″ to 57″
Reel max width	32″	31.5″	42″	37″ to 55″
Reel min width	32″	20″	21″	37″ to 55″
Max capacity lb.	6,000 Lb.	Varies	5,000 Lb.	Varies
Material	Steel	Wood w/Steel Shaft	Steel w/Wooden Reel	Steel

*SIM*pull*™ Reel covers should be used with the SIM*pull*™ Reel to prevent damage to floors

Southwire®

©2024 Southwire Company, LLC. All Rights Reserved.