

# Re<sup>3</sup><sup>™</sup> SIMpull XHHW-2<sup>®</sup>/RW90 Aluminum

WITH 2-LETTER COLOR CODES TO AID COLOR BLINDNESS

Southwire's Re<sup>3</sup><sup>™</sup> SIMpull XHHW-2<sup>®</sup>/RW90 Aluminum cable features bold, two-letter color codes printed directly on the insulation to simplify identification, aid color blindness, and prevent misidentification during installation, operation, and maintenance.

## FEATURES

- Suitable for use in wet or dry locations at temperatures not to exceed 90°C. Voltage for all applications is up to 1000 volts
- Easy to identify two-letter color codes printed on the insulation for colorblind electricians and electrical contractors
- Triple rated for U.S. Canada, and Mexico
- Patented formulation to create a reduced Coefficient of Friction (COF) for the most efficient pulling

## SPECIFICATIONS:

- ASTM B800 8000 Series Aluminum Alloy Wire
- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- NMX-J-451-ANCE Thermoset insulated wires and cables
- NOM-063-SCFI Electrical Products – Conductors – Safety Requirements



**SCAN HERE**

TO ACCESS  
SPEC 10016

