

Copper Building Wire

Date: April 10, 2026

Prices shown are per 1000 feet. Subject to change without notice. This sheet supersedes Sheet #0327026-C dated March 27, 2026.

| Size | THHN COLORS | THHN BLACK | USE | XHHW | TFFN | TFN |
|-----------------|----------------|---------------|------------|-----------|----------|----------|
| SOLID | | | | | | |
| 18 AWG | ---- | ---- | ---- | ---- | ---- | \$154.95 |
| 16 | ---- | ---- | ---- | ---- | ---- | 215.04 |
| 14 | \$312.81 | | ---- | ---- | ---- | ---- |
| 12 | 479.90 | | \$866.09 | ---- | ---- | ---- |
| 10 | 750.83 | | ---- | ---- | ---- | ---- |
| STRANDED | | | | | | |
| 18 AWG | ---- | ---- | ---- | ---- | \$189.00 | ---- |
| 16 | ---- | ---- | ---- | ---- | 264.45 | ---- |
| 14 | \$347.90 | | \$872.21 | \$468.50 | ---- | ---- |
| 12 AWG | 514.09 | | 926.24 | 636.02 | ---- | ---- |
| 10 | 786.32 | | 1,128.89 | 953.18 | ---- | ---- |
| 8 | 1,459.49 | | 2,016.71 | 1,692.40 | ---- | ---- |
| 6 | 2,245.53 | | 2,910.25 | 2,570.83 | ---- | ---- |
| 4 AWG | 3,436.30 | | 4,434.21 | 3,782.96 | ---- | ---- |
| 3 | 4,334.26 | | ---- | 4,649.94 | ---- | ---- |
| 2 | 5,425.13 | 5,425.13 | 6,889.61 | 5,838.08 | ---- | ---- |
| 1 | 6,218.01 | 6,218.01 | 7,599.86 | 6,586.76 | ---- | ---- |
| 1/0 AWG | 7,612.93 | 7,612.93 | 9,693.69 | 8,096.17 | ---- | ---- |
| 2/0 | 9,377.62 | 9,377.62 | 12,185.20 | 10,118.09 | ---- | ---- |
| 3/0 | 11,834.91 | 11,834.91 | 15,226.92 | 12,666.66 | ---- | ---- |
| 4/0 | 14,773.05 | 14,773.05 | 19,017.34 | 15,886.46 | ---- | ---- |
| 250 kcmil | 17,118.30 | 17,118.30 | 20,432.67 | 18,321.68 | ---- | ---- |
| 300 | 20,529.08 | 20,529.08 | 23,342.59 | 21,782.67 | ---- | ---- |
| 350 | 24,037.63 | 24,037.63 | 27,732.65 | 25,450.18 | ---- | ---- |
| 400 | 27,344.02 | 27,344.02 | 31,446.20 | 29,021.33 | ---- | ---- |
| 500 kcmil | 34,551.17 | 34,551.17 | 38,102.60 | 36,197.57 | ---- | ---- |
| 600 | 43,054.04 | 0.00 | 47,449.06 | 45,709.29 | ---- | ---- |
| 750 | 72,777.90 | 72,777.90 | 77,342.57 | 74,487.46 | ---- | ---- |
| 1000 | 96,579.46 | 96,579.46 | 102,419.11 | 97,777.02 | ---- | ---- |

| THHN with stripes Standard Colors Only | |
|--|----------|
| WHT-BLK, WHT-RED, WHT-BLU, GRN-YEL GRY-BRN, GRY-ORN, GRY-YEL, GRY-PUR | |
| 12 SOLID THHN With Stripes | \$575.42 |
| 12 STRANDED THHN With Stripes | 609.75 |
| 10 SOLID THHN With Stripes | 846.41 |
| 10 STRANDED THHN With Stripes | 881.87 |

| Cutting and Paralleling Charges Per Reel | Cutting Only 1 Conductor | Paralleling 2 Conductors |
|---|-----------------------------|-----------------------------|
| Sizes AWG 18-AWG 10 | STD PKG ONLY | STD PKG ONLY |
| Sizes AWG 8- 500 kcmil | \$90.00 | \$180.00 |
| Sizes 600 kcmil - 1000 kcmil | \$90.00 | \$180.00 |

| Cutting and Paralleling Charges Per Reel | Paralleling 3 conductors | Paralleling 4 conductors |
|---|-----------------------------|-----------------------------|
| Sizes AWG 18-AWG 10 | STD PKG ONLY | STD PKG ONLY |
| Sizes AWG 8- 500 kcmil | \$270.00 | \$360.00 |
| Sizes 600 kcmil - 1000 kcmil | \$270.00 | \$360.00 |

(Paralleling charge includes the cost for cutting. An additional charge of \$20.00 will apply to any cuts less than 250 feet shipped on reels.)

Notes:

THHN, USE, XHHW, TFFN & TFN Products carry multiple ratings. (Please see Southwire catalog for detailed information.)

THHN, sizes 14 and 12, are packaged 4-500ft.spools (2000 ft.) /ctn.

THHN, size 10, is packaged 2-500ft. spools (1000 ft.) /ctn.

TFFN & TFN sizes 18 and 16, are packaged 4-500ft. spools (2000 ft.) /ctn.

Orders for items packaged in ctns. must be in ctn. multiples.

AWG - American Wire Gauge.

Kcmil - Thousand Circular-mils.

"Call Southwire for all your wire & cable needs"



Copper Building Wire

PRICING

Net Selling Prices will be determined by multiplying a four-decimal-place Multiplier (i.e. .9999) against the list price.

PAYMENT TERMS

Terms are 2% 10th prox. month, net end of prox. month.

ORDER ACCEPTANCE

Orders are binding only after acceptance by the General Office in Carrollton and all transactions are subject to Southwire's General Terms and Conditions. Orders will be invoiced on date of shipment.

MINIMUM ORDER

The minimum order amount is \$1,000 and can be any combination of products.

DELIVERY TERMS

Orders of 5,000 pounds or more net weight will be FOB Shipping Point, freight prepaid and allowed, within the continental United States only. Orders f.o.b. ports of Alaska or Hawaii subject to an additional shipping cost. Rates for "Prepay and Charge" orders are based on the (1994) Yellow YFSY 500M tariff with a 30% discount, with an absolute minimum charge of \$72.00.

For Prepaid Freight information for combinations of products, please see The "Southwire Standard Freight Policy" at <https://www.southwire.com/freight-policy>, or you may contact your sales representative.

RETURN GOODS REQUEST

Southwire building wire products are carefully manufactured, tested and labeled per Underwriters Laboratories specifications. Should our products prove defective, or appear to be so, please discontinue use immediately and notify us so an inspection can be made. We cannot be responsible for any damages or claims beyond the selling price of our products.

FOR ADDITIONAL INFORMATION

For product data on Southwire copper building wire see Catalog Section 1 or www.southwire.com. For General Terms and Conditions of Sale see Catalog Section 63. For additional information on these or any other Southwire products, contact your Southwire representative or Southwire Company, Building Wire Sales, in Carrollton, Georgia.



Carrollton, Georgia 30119-0001, USA
Phone: 1-800-444-1700
Fax: (770) 838-6543