



Leadwire Quick Reference

July 10, 2025

All prices shown are per 1000 Feet. Cut charges may apply. Pricing subject to change without notice. Please refer to Southwire's full terms and conditions <https://www.southwire.com/TermsAndConditions>
For Stock Use Only

SIZE	MTW			
	Bare	Bare w/Extruded stripe	Bare w/Spiral stripe	Bare w/Two stripes
20-10	\$ 83.75		\$ 145.00	
18-16	\$ 99.00	\$ 102.06	\$ 170.00	
16-26	\$ 138.36	\$ 141.15		\$ 141.15
14-41	\$ 211.76	\$ 213.76	\$ 294.03	\$ 213.76
14-19	\$ 211.76	\$ 229.00		
12-65	\$ 283.90	\$ 285.90		
12-19	\$ 283.90	\$ 305.00	\$ 342.00	
10-105	\$ 439.61	\$ 441.61	\$ 441.61	\$ 441.61
10-19	\$ 439.61	\$ 441.61	\$ 475.00	\$ 441.61
8-19	\$ 778.74	\$ 781.74		
6-19	\$ 1,246.42	\$ 1,246.42		
6-133	\$ 1,246.42			
4-19	\$ 2,002.89			
4-133	\$ 2,002.89			\$ 2,002.89
2-19	\$ 2,929.97			
2-133	\$ 2,929.97			\$ 3,029.97
1/0-19	\$ 4,668.30			
1/0-259	\$ 4,668.30			
2/0-19	\$ 5,366.40			
2/0-259	\$ 5,700.00			
3/0-19	\$ 6,501.60			
3/0-259	\$ 6,701.60			
4/0-37	\$ 8,359.20			
4/0-259	\$ 8,359.20			
250-2451	\$ 11,023.00			
350-3458	\$ 13,682.73			
400-269	\$ 16,475.69			
500-5054	\$ 20,567.62			

WELDING CABLE			
SIZE	UL/CSA	NON-UL/CSA	ROYAL SUPER EXCELENE ORANGE
6	\$ 1,450.00		\$ 2,190.00
4	\$ 2,200.00		\$ 2,989.27
2	\$ 2,846.00		\$ 4,093.36
1	\$ 4,150.00		\$ 5,211.00
1/0	\$ 4,760.00		\$ 6,898.00
2/0	\$ 6,210.00		\$ 8,153.75
3/0	\$ 7,442.00		\$ 10,171.00
4/0	\$ 9,272.00		\$ 13,931.00
250		\$ 12,472.00	
350		\$ 14,990.00	
500		\$ 22,100.00	

SPT-1 (LAMP CORD)			
Size	CU	STC	STC/CU
18/2	\$ 314.15	\$ 314.15	\$ 314.15

SPT-2 (LAMP CORD)			
Size	CU		
16/2	\$ 508.41		

BATTERY CABLE				
Size	SXL	SGT (80C)	SGT (105C)	SGX
20-7	\$ 90.75			
18-19	\$ 103.33			
18-16	\$ 117.03			
16-19	\$ 158.00			
14-19	\$ 232.02			
12-19	\$ 327.36			
10-19	\$ 527.76			
8-19	\$ 924.27			
6-133	-		\$ 1,380.96	\$ 1,475.80
4-133	-	\$ 2,157.62	\$ 2,406.00	\$ 2,289.05
2-133	-		\$ 3,249.58	\$ 3,399.07
1-259	-		\$ 4,037.20	\$ 4,050.00
1/0-19	-		\$ 5,198.57	
1/0-1026	-			\$ 5,646.75
2/0-19	-		\$ 5,986.00	
2/0-1254	-			\$ 6,925.06
3/0-19	-	\$ 7,826.75	\$ 7,644.54	\$ 8,431.21
4/0-2109	-		\$ 9,902.94	\$ 10,815.12

SIS Cable XHHW-2 VW-1	
SIZE	Tinned
18-16	-
16-26	-
14-41	\$ 317.05
12-65	\$ 461.68
10-105	\$ 600.00
8-133	\$ 1,590.00
6-19	\$ 2,000.00
4-19	\$ 2,900.00
2-19	\$ 4,000.00
1/0-19	\$ 6,015.00
2/0-19	\$ 7,400.00
3/0-19	\$ 9,000.00
4/0-19	\$ 11,000.00

AWM Series 1000																		
Appliance																		
1569		1015					1283		1284		1028		1056		1060		1061	1232/1284/ 1338/10269
SIZE	Bare	Tinned	Bare	Tinned	Tinned (1-SPS)	Tinned (2-SPS)	Bare	Tinned	Bare	Tinned	Bare	Tinned	Bare	Tinned	Bare	Tinned	Tinned	Tinned
24	\$ 66.59	\$ 44.90																\$ 50.10
22	\$ 58.43	\$ 55.43	\$ 64.91	\$ 60.52	\$ 91.89	\$ 91.89												\$ 54.49
20	\$ 67.19	\$ 73.42	\$ 83.75	\$ 85.00	\$ 130.00													\$ 76.13
18	\$ 94.22	\$ 93.94	\$ 113.91	\$ 107.58	\$ 135.00									\$ 99.00	\$ 164.54			\$ 96.31
16	\$ 140.63	\$ 153.79	\$ 138.36	\$ 211.99	\$ 230.00									\$ 209.20	\$ 211.99			\$ 144.04
14	\$ 208.68	\$ 195.80	\$ 210.00	\$ 217.99	\$ 250.00										\$ 297.51	\$ 347.11	\$ 350.83	
12	\$ 291.17	\$ 310.97	\$ 283.90	\$ 325.00	\$ 400.00	\$ 325.00					\$ 368.64					\$ 453.00		
10			\$ 439.61	\$ 470.00		\$ 505.00					\$ 509.45	\$ 578.80	\$ 578.78		\$ 658.69	\$ 624.33		
8-19											\$ 778.74	\$ 949.24						
8-133											\$ 953.94	\$ 993.43						
6							\$ 1,246.42	\$ 1,497.92										
6-133																		\$ 1,592.41
4							\$ 2,002.89	\$ 2,066.15										
4-133																		\$ 2,066.15
2																		
2-133							\$ 2,929.97	\$ 3,027.55										\$ 3,027.55
1											\$ 3,866.94							\$ 3,866.94
1/0									\$ 4,668.30	\$ 4,670.00								\$ 4,670.00
2/0									\$ 5,700.00	\$ 5,799.53								\$ 5,799.53
3/0									\$ 6,701.60	\$ 6,900.00								\$ 6,900.00
4/0									\$ 8,359.20	\$ 8,565.60								\$ 8,565.60
250										\$ 10,449.00								\$ 10,449.00

AWM Series 3000							Automotive					
Appliance							TWP	GPT (80C)	GPT (105C)	TXL	GXL	
3173		3321			3271	3340						
SIZE	Bare	Tinned	Bare	Tinned	Tinned	Tinned	SIZE	Bare	Bare	Bare	Bare	Bare
22	\$ 72.68	\$ 71.59		\$ 87.63			22	\$ 48.43			\$ 63.66	
20		\$ 124.20		\$ 109.19			20	\$ 72.35	\$ 75.92	\$ 76.50	\$ 78.69	\$ 81.66
18	\$ 132.19	\$ 115.00	\$ 136.35	\$ 136.54	\$ 335.77	\$ 298.74	18-16	\$ 102.57	\$ 114.05	\$ 118.13	\$ 104.31	\$ 116.04
18-19							18-19	\$ 93.99	\$ 90.08		\$ 156.59	\$ 107.90
16	\$ 174.93	\$ 183.13	\$ 179.83	\$ 195.00	\$ 300.67	\$ 511.87	16	\$ 133.15	\$ 140.10	\$ 143.12	\$ 138.00	\$ 163.00
14	\$ 240.80	\$ 278.88	\$ 310.29	\$ 255.05	\$ 496.43	\$ 412.41	14	\$ 172.07	\$ 230.27	\$ 211.54	\$ 205.70	\$ 234.33
12	\$ 360.00	\$ 400.00	\$ 379.02	\$ 393.43	\$ 650.00	\$ 735.00	12	\$ 271.87	\$ 332.75	\$ 321.69	\$ 315.53	\$ 311.56
10	\$ 554.41	\$ 585.00	\$ 570.17	\$ 638.30	\$ 819.52	\$ 900.00	10	\$ 410.76	\$ 489.56	\$ 501.43	\$ 490.25	\$ 775.00
8				\$ 1,278.94	\$ 1,704.94	\$ 1,512.94	8		\$ 872.69	\$ 821.23	\$ 799.30	\$ 934.00
6					\$ 2,373.29	\$ 2,059.09	6					
4					\$ 3,015.00	\$ 2,900.71	4					
2					\$ 4,174.00	\$ 4,824.86	2					
1					\$ 5,375.00	\$ 4,844.00	1					
1/0						\$ 6,152.69	1/0					
2/0						\$ 7,715.42	2/0					
3/0						\$ 9,941.73	3/0					
4/0						\$ 11,503.02	4/0					

Grounding		
Size	Yellow	Orange
1/0-1045	\$ 4,838.90	
2/0-1254		
2/0-1330	\$ 6,158.13	
2/0-3325		
4/0-2109	\$ 9,420.39	