



# Leadwire Quick Reference

## September 26, 2025

All prices shown are per 1000 Feet. Cut charges may apply. Pricing subject to change without notice. Please refer to Southwire's full terms and conditions <https://www.southwire.com/TermsAndConditions>

For Stock Use Only

PH	E00E10	E00E20	E00E30	E00E40	E00E50	E00E90
	1/C PVC	1/C XLP	Multi-Cdr PVC	Welding	Grounding	High Temp
<b>Multiplier</b>	<b>1.0000</b>	<b>1.0000</b>	<b>1.0000</b>	<b>1.0000</b>	<b>1.0000</b>	
Discount %	0.00%	0.00%	0.00%	0.00%	0.00%	

SIZE	MTW			
	Bare	Bare w/Extruded stripe	Bare w/Spiral stripe	Bare w/Two stripes
20-10	\$ 83.75		\$ 145.00	
18-16	\$ 99.27	\$ 102.06	\$ 170.00	
16-26	\$ 138.36	\$ 141.15		\$ 141.15
14-41	\$ 211.76	\$ 213.76	\$ 294.03	\$ 294.03
14-19	\$ 211.76	\$ 294.03		
12-65	\$ 320.00			
12-19	\$ 283.90	\$ 305.00	\$ 342.00	
10-105	\$ 500.00	\$ 502.50	\$ 502.50	\$ 505.50
10-19	\$ 439.61	\$ 441.61	\$ 475.00	\$ 475.00
8-19	\$ 778.74	\$ 778.74		
6-19	\$ 1,325.00	\$ 1,327.50		
6-133	\$ 1,246.42			
4-19	\$ 2,105.00			
4-133	\$ 2,002.89			\$ 2,002.89
2-19	\$ 3,310.00			
2-133	\$ 2,929.97			\$ 3,029.97
1/0-19	\$ 4,668.30			
1/0-259	\$ 4,668.30			
2/0-19	\$ 5,366.40			
2/0-259	\$ 5,700.00			
3/0-19	\$ 6,501.60			
3/0-259	\$ 6,701.60			
4/0-37	\$ 8,359.20			
4/0-259	\$ 8,359.20			
250-2451	\$ 11,023.00			
350-3458	\$ 13,682.73			
400-269	\$ 16,475.69			
500-5054	\$ 20,567.62			

WELDING CABLE			
SIZE	UL/CSA	NON-UL/CSA	ROYAL SUPER EXCELENE ORANGE
6	\$ 1,450.00		\$ 2,190.00
4	\$ 2,200.00		\$ 2,989.27
2	\$ 2,846.00		\$ 4,093.36
1	\$ 4,150.00		\$ 5,211.00
1/0	\$ 4,760.00		\$ 6,898.00
2/0	\$ 6,210.00		\$ 8,153.75
3/0	\$ 7,442.00		\$ 10,171.00
4/0	\$ 9,272.00		\$ 13,931.00
250		\$ 12,472.00	
350		\$ 14,990.00	
500		\$ 22,100.00	

SPT-1 (LAMP CORD)			
Size	CU	STC	STC/CU
18/2	\$ 314.15	\$ 314.15	\$ 314.15

SPT-2 (LAMP CORD)			
Size	CU		
16/2	\$ 508.41		

BATTERY CABLE				
Size	SXL	SGT (80C)	SGT (105C)	SGX
20-7	\$ 90.75			
18-19	\$ 103.33			
18-16	\$ 117.03			
16-19	\$ 158.00			
14-19	\$ 232.02			
12-19	\$ 327.36			
10-19	\$ 527.76			
8-19	\$ 924.27			
6-133	-		\$ 1,380.96	\$ 1,475.80
4-133	-	\$ 2,157.62	\$ 2,406.00	\$ 2,289.05
2-133	-		\$ 3,249.58	\$ 3,399.07
1-259	-		\$ 4,037.20	\$ 4,050.00
1/0-19	-		\$ 5,198.57	
1/0-1026	-			\$ 5,646.75
2/0-19	-		\$ 5,986.00	
2/0-1254	-			\$ 6,925.06
3/0-19	-	\$ 7,826.75	\$ 7,644.54	\$ 8,431.21
4/0-2109	-		\$ 9,902.94	\$ 10,815.12

SIS Cable XHHW-2 VW-1	
SIZE	Tinned
18-16	-
16-26	-
14-41	\$ 317.05
12-65	\$ 461.68
10-105	\$ 600.00
8-133	\$ 1,590.00
6-19	\$ 2,000.00
4-19	\$ 2,900.00
2-19	\$ 4,000.00
1/0-19	\$ 6,015.00
2/0-19	\$ 7,400.00
3/0-19	\$ 9,000.00
4/0-19	\$ 11,000.00

AWM Series 1000																		
Appliance																		
	1569		1015				1283		1284		1028		1056		1060		1061	1232/1284/ 1338/10269
SIZE	Bare	Tinned	Bare	Tinned	Tinned (1-SPS)	Tinned (2-SPS)	Bare	Tinned	Bare	Tinned	Bare	Tinned	Bare	Tinned	Bare	Tinned	Tinned	Tinned
24	\$ 66.59	\$ 44.90																\$ 50.10
22	\$ 58.43	\$ 55.43	\$ 64.91	\$ 60.52	\$ 91.89	\$ 91.89												\$ 54.49
20	\$ 67.19	\$ 73.42	\$ 83.75	\$ 85.00	\$ 130.00													\$ 76.13
18	\$ 94.22	\$ 93.94	\$ 113.91	\$ 107.58	\$ 135.00								\$ 99.00	\$ 164.54				\$ 96.31
16	\$ 140.63	\$ 153.79	\$ 138.36	\$ 211.99	\$ 230.00								\$ 209.20	\$ 211.99				\$ 144.04
14	\$ 208.68	\$ 195.80	\$ 210.00	\$ 217.99	\$ 250.00										\$ 347.11	\$ 350.83		
12	\$ 291.17	\$ 310.97	\$ 320.00		\$ 400.00						\$ 368.64				\$ 453.00			
10			\$ 439.61	\$ 470.00		\$ 505.00					\$ 439.61	\$ 578.80	\$ 578.78		\$ 658.69	\$ 624.33		
8-19											\$ 778.74	\$ 949.24						
8-133											\$ 953.94	\$ 993.43						
6							\$ 1,246.42	\$ 1,497.92										
6-133																		\$ 1,564.42
4							\$ 2,002.89	\$ 2,066.15										
4-133																		\$ 2,066.15
2																		
2-133							\$ 2,929.97	\$ 3,027.55										\$ 3,027.55
1											\$ 3,866.94							\$ 3,866.94
1/0									\$ 4,668.30	\$ 4,670.00								\$ 4,670.00
2/0									\$ 5,700.00	\$ 5,799.53								\$ 5,799.53
3/0									\$ 6,701.60	\$ 6,900.00								\$ 6,900.00
4/0									\$ 8,359.20	\$ 8,565.60								\$ 8,565.60
250									\$ 10,449.00									\$ 10,449.00

AWM Series 3000							Automotive					
Appliance												
	3173		3321		3271	3340		TWP	GPT (80C)	GPT (105C)	TXL	GXL
SIZE	Bare	Tinned	Bare	Tinned	Tinned	Tinned	SIZE	Bare	Bare	Bare	Bare	Bare
22	\$ 72.68	\$ 71.59		\$ 87.63			22	\$ 48.43			\$ 63.66	
20		\$ 124.20		\$ 109.19			20	\$ 72.35	\$ 75.92	\$ 76.50	\$ 78.69	\$ 81.66
18	\$ 132.19	\$ 115.00	\$ 136.35	\$ 136.54	\$ 335.77	\$ 298.74	18-16	\$ 102.57	\$ 114.05	\$ 118.13	\$ 104.31	\$ 116.04
18-19							18-19	\$ 93.99	\$ 90.08		\$ 156.59	\$ 107.90
16	\$ 174.93	\$ 183.13	\$ 179.83	\$ 195.00	\$ 300.67	\$ 511.87	16	\$ 133.15	\$ 140.10	\$ 143.12	\$ 138.00	\$ 163.00
14	\$ 240.80	\$ 278.88	\$ 310.29	\$ 255.05	\$ 496.43	\$ 412.41	14	\$ 172.07	\$ 230.27	\$ 211.54	\$ 205.70	\$ 234.33
12	\$ 360.00	\$ 400.00	\$ 379.02	\$ 393.43		\$ 735.00	12	\$ 271.87	\$ 332.75	\$ 321.69	\$ 315.53	\$ 311.56
10	\$ 554.41	\$ 585.00	\$ 570.17	\$ 638.30	\$ 819.52	\$ 900.00	10	\$ 410.76	\$ 489.56	\$ 501.43	\$ 490.25	\$ 775.00
8				\$ 1,278.94	\$ 1,704.94	\$ 1,512.94	8		\$ 872.69	\$ 821.23	\$ 799.30	\$ 934.00
6						\$ 2,059.09	6					
4					\$ 3,015.00	\$ 2,900.71	4					
2					\$ 4,174.00	\$ 4,824.86	2					
1					\$ 5,375.00	\$ 4,844.00	1					
1/0						\$ 6,152.69	1/0					
2/0						\$ 7,715.42	2/0					
3/0						\$ 9,941.73	3/0					
4/0						\$ 11,503.02	4/0					

Grounding	
Size	Yellow
1/0-1045	\$ 4,838.90
2/0-1254	
2/0-1330	\$ 6,158.12
2/0-3325	
4/0-2109	\$ 9,420.38