

Effective Date: September 19, 2019

Supersedes sheet SS38

Prices shown are per 1,000 feet. Subject to change without notice.

**Duraclad Steel Armor MC**

Copper Conductor MC Cable

Size	Package Quantity	Feet Per Pallet	Product Weight/MFT	OD (Inches)	List Price
<b>SOLID</b>					
14-2c STL	250'	11250	115	0.447	\$1,172.67
14-2c STL	1000'	5000	115	0.447	\$1,202.67
14-3c STL	250'	11250	138	0.464	\$1,832.29
14-3c STL	1000'	5000	138	0.464	\$1,862.29
14-4c STL	250'	11250	154	0.502	\$2,554.10
12-2c STL	250'	11250	142	0.475	\$1,182.68
12-2c STL	1000'	5000	142	0.475	\$1,212.64
12-3c STL	250'	11250	172	0.513	\$2,026.64
12-3c STL	1000'	5000	172	0.513	\$2,056.60
12-4c STL	250'	6250	201	0.547	\$2,742.88
12-4c STL	1000'	4000	201	0.547	\$2,772.88
10-2c STL	250'	6250	197	0.55	\$2,516.34
10-2c STL	1000'	4000	197	0.55	\$2,546.34
10-3c STL	250'	6250	240	0.588	\$3,525.78
10-3c STL	1000'	4000	240	0.588	\$3,555.74
10-4c STL	250'	6250	284	0.631	\$5,535.74
10-4c STL	1000'	4000	284	0.631	\$5,565.70
<b>STRANDED</b>					
12-2c STR STL	250	9000	157	0.495	\$1,485.82
12-2c STR STL	1000	5000	157	0.495	\$1,515.82
12-3c STR STL	250	6250	187	0.527	\$2,299.82
12-3c STR STL	1000	4000	187	0.527	\$2,332.00
10-2c STR STL	1000	4000	213	0.566	\$3,039.39
10-2c STR STL	1000	4000	213	0.566	\$3,039.39
8-2c #10 g STL	1000'		277	0.642	\$3,195.98
8-2c #10 g STL	1000'		277	0.642	\$3,195.98
8-3c #10 g STL	500'		357	0.732	\$4,496.58
8-3c #10 g STL	1000'		357	0.732	\$4,496.58
6-2c #8 g STL	500'		467	0.754	\$4,732.19
6-2c #8 g STL	1000'		467	0.754	\$4,732.19

## Duraclad Steel Armor AC

Size	Package Quantity	Feet Per Pallet	Product Weight/MFT	OD (Inches)	List Price
<b>SOLID</b>					
14-2c AC STL	250'	11250	185	0.46	\$1,154.90
14-2c AC STL	1000'	5000	185	0.46	\$1,184.90
14-3c AC STL	250'	7500'	209	0.485	\$1,798.97
14-3c AC STL	1000'	5000	209	0.485	\$1,828.97
14-4c AC STL	250'	7500'	237	0.517	\$2,509.68
12-2c AC STL	250'	11250	213	0.498	\$1,166.00
12-2c AC STL	1000'	5000	213	0.498	\$1,196.00
12-3c AC STL	250'	11250	246	0.521	\$1,913.37
12-3c AC STL	1000'	5000	246	0.521	\$2,035.52
12-4c AC STL	250'	7500'	283	0.557	\$2,737.34
12-4c AC STL	1000'	4000	283	0.557	\$2,767.30
10-2c AC STL	250'	7500'	264	0.56	\$2,158.76
10-2c AC STL	1000'	4000	264	0.56	\$2,188.77
10-3c AC STL	250'	7500'	312	0.588	\$3,010.52
10-3c AC STL	1000'	4000	312	0.588	\$3,040.49
10-4c AC STL	250'	7500'	366	0.632	\$4,676.24
10-4c AC STL	1000'	4000'	366	0.632	\$4,706.20
<b>STRANDED</b>					
8-2c AC STL	500'		365	0.686	\$4,590.70
8-3c AC STL	500'		556	0.834	\$5,971.05
8-4c AC STL	500'		653	0.895	\$8,519.57
6-3c AC STL	100'		696	0.912	\$8,646.17
6-4c AC STL	100'		830	0.981	\$11,457.90
4-3c AC STL	100'		948	1.07	\$12,476.22
4-4c AC STL	500'		1150	1.15	\$16,995.86
2-3c AC STL	1000'		1265	1.19	\$17,748.76
2-4c AC STL	100'		1559	1.293	\$23,764.19



### Duraclad Steel Armor MC-AP HCF

Size	Package Quantity	Feet Per Pallet	Product Weight/MFT	OD (Inches)	List Price
<b>SOLID CONDUCTORS</b>					
12-2c STL HCF	250'	N/A	170	0.447	\$1,963.32
12-2c STL HCF	1000'	N/A	170	0.447	\$1,993.32
12-3c STL HCF	250'	N/A	201	0.481	\$2,895.03
12-3c STL HCF	1000'	N/A	201	0.481	\$2,924.99
12-4c STL HCF	250'	N/A	233	0.516	\$4,366.39
12-4c STL HCF	1000'	N/A	233	0.516	\$4,396.40
10-2c STL HCF	250'	N/A	234	0.522	\$3,118.22
10-2c STL HCF	1000'	N/A	234	0.522	\$3,317.01
10-3c STL HCF	250'	N/A	294	0.625	\$4,845.03
10-3c STL HCF	1000'	N/A	294	0.625	\$4,874.99
10-4c STL HCF	1000'		346	0.67	\$6,499.64
<b>STRANDED CONDUCTORS</b>					
12-2c STR STL HCF	250'	N/A	180	0.469	\$2,369.75
12-2c STR STL HCF	1000'	N/A	180	0.469	\$2,399.76
12-3c STR STL HCF	250'	N/A	213	0.506	\$3,389.17
12-3c STR STL HCF	1000'	N/A	213	0.506	\$3,419.18

### Duraclad Steel - Bare Conductor

Size	Package Quantity	Feet Per Pallet	Product Weight/MFT	OD (Inches)	List Price
<b>SOLID</b>					
8-1c BAG STL	250'	6000	197	0.46	\$1,705.31
8-1c BAG STL	1000'	4000	197	0.46	\$1,705.31
6-1c BAG STL	250'	6000	235	0.485	\$2,045.18
6-1c BAG STL	1000'	4000	235	0.485	\$2,045.18
<b>STRANDED</b>					
4-1c BAG STL	250'	7500	295	0.515	\$3,273.46
4-1c BAG STL	750'	4000	295	0.515	\$3,273.46



---

## **TECHNICAL STANDARDS**

Type MC is manufactured per UL Standard 1569 NEC Article #334.

## **PAYMENT TERMS**

Terms are 2% 10<sup>th</sup> prox. month, net end of prox. month. Cut off dates have been moved from the 25th to the 30th. Any invoices with dates for days 1-30 of the month are due with discount by the 10th of the month following the invoice month, and are due net by the last day of the month following the invoice month.

(Example: Invoice date of 03/30, due with discount on 04/10, and due net by 04/30.)

Any invoices dated the 31<sup>st</sup> of a month are due with discount by the 10th of the second month following the invoice month, and are due net by the last day of the second month following the invoice month.

(Example: Invoice date of 03/31, due with discount on 05/10, and due net by 05/31.)

## **ORDER ACCEPTANCE**

Orders are binding only after acceptance by the General Office in Carrollton and all transactions are subject to Southwire's General Terms and Conditions. Orders will be invoiced on date of shipment.

## **MINIMUM ORDER**

The minimum order amount is \$1,000 and can be any combination of products. An additional \$45.00 cutting charge per reel is applicable on non-stock lengths.

## **DELIVERY TERMS**

Orders of

For Prepaid Freight information for combinations of products, please see The "Electrical Division Freight Policy"

Policy" on the southwire.com home page, or the "Document Summary" from the internet price sheet page, or you may contact your sales representative.

## **RETURN GOODS REQUEST**

Southwire EZ-

## **REEL CHARGES**

An additional charge per reel is applicable on Copper EZ-MC products.

Any cut length of MC size 2 and larger less than 250 feet, may require a \$200 miscellaneous reel charge

## **SPECIAL REQUIREMENTS**

For special sizes, strandings, colors, conductor counts or lengths, please contact your Southwire representative.

**Carrollton, Georgia 30119-0001, USA Phone:**

**(770) 832-4153**

