



BENDstation[™] **RIGID WORKSTATION**

Comprehensive conduit bending workstation for 3/4" & 1" RIGID & IMC



RB1000

BUILT-IN PROTRACTOR FOR QUICK AND ACCURATE BENDS

Increase bending speed on the job

SAFE AND EFFICIENT

Measuring, bending and cutting at a 36" table height

HIGH CAPACITY

Store up to 700 feet of conduit

BUILT-IN RATCHET SYSTEM

Bending requires up to 40% less force to bend than other mechanical benders

HIGHLY MOBILE

Heavy-duty casters for easy transportation and mobility

BENDstation™ RIGID WORKSTATION

- · More accurate measurements, bends, and cuts
- Built-in protractor for quick and accurate bends
- Comfortable work table height at 36"
- The ability to store up to 700 feet of conduit, strut or 1000 lbs of other materials
- Extra shelf for storage of tools and materials
- Heavy duty casters for easy transportation and mobility
- · Less labor fatigue; work standing up without constantly bending over
- Dual-bending shoe designed for both 3/4" and 1" rigid and IMC
- Bending requires up to 40% less force to bend than other mechanical benders
- A 60" ruler is incorporated on the working surface for quick and accurate marking
- Side mounted chain vise is easily adjustable to multiple positions for quicker and safer cutting and threading

SPECIFICATIONS

MODEL #	STOCK#	UPC#	LENGTH	WIDTH	HEIGHT	WEIGHT
RB1000	59840701	0-32886-96048-2	29"	69"	38.5"	170 lbs.
DESCRIPTION BENDstation™ for 3/4" and 1" rigid and IMC						



BENDING SERIES RB1000

