

OUR STORY

As a family business, Southwire proudly continues building on our commitment to environmental stewardship and corporate sustainability by prioritizing stakeholder expectations, and supporting the wellbeing of our communities and the environment in which we live. To help us meet this commitment, we organize our sustainability strategy around five core tenets: Growing Green, Living Well, Giving Back, Doing Right, and Building Worth.

We Deliver Power...Responsibly®

We remain committed to the sustainability of our company for the next 100 years and beyond. As we strengthen this commitment, we continue to work hard every day to discover, develop and distribute sustainable solutions that exceed the expectations of our stakeholders around the world.

OUR MISSION

To be a preferred provider of solutions to the electrical industry by providing innovative products and services with exceptional quality.

OUR VALUES

Our **ONE Southwire** culture prioritizes the interests of our team members, customers, and communities through a continuous commitment to empowerment, trust, consistency, and inclusion.

OUR REACH

Nearly one in two new homes built in the United States contains our wire, and we produce half of the cable used to transmit and distribute electricity throughout the nation.

OUR PRODUCTS

Our product teams and dedicated resources work together to listen to and work with our customers, creating solutions that deliver unparalleled value through product innovation, safety and efficiency.

OUR SERVICE

Service is more than a word or a phone number; it's a tangible support system that assists you through the entire project cycle; from our knowledgeable customer service team, to our experienced field sales team, we're there every step of the way.



TABLE OF CONTENTS

TEMPORARY LIGHTING

Area Lights	3
Overhead Lights	
String Lights	
Cart Lights	
Work Lights	
Personal Lighting	
Clamps & Trouble Lights	
Installed Lighting	
Hazardous Location	

The Southwire Area Lighting range is built to offer maximum lumen output for large projects, while still keeping lighting at ground level. Included in this category group is the Wobblelight product group, featuring self-righting technology, and the ability to output light at 360°. Additionally, the balloon light category offers the latest in LED technology on heavy-duty stands to ensure the light is away from eye level. Southwire can light any jobsite with the perfect 360° lighting solution for you.





For 20 years, the Wobblelight® has provided reliable lighting on the jobsite. The self-righting technology paired with heavy-duty housing guarantees these products will provide years of service in the toughest environments.



LED WOBBLELIGHT®



• 120V

- Operating temp: -40°F to 125°F
- 5000K color temperature
- 5-15 plug

SPECIFICATIONS

MODEL #	DESCRIPTION	BODY STYLE	WATTS	LAMP LIFE	LINKABLE UNITS	AMP DRAW	CORD TYPE	IP RATING	WEIGHT
111301LED	12,000 lumen 32" LED Wobblelight	32"	150W	50,000 hrs.	6 Max	1.25A	5' 16/3 SJ00W	IP54	31 lbs.
111303LED	15,000 lumen 32" LED Wobblelight	32"	220W	50,000 hrs.	-	1.8A	5' 16/3 SJ00W	IP55	31 lbs.

10,000 LUMEN SELF-RIGHTING LED JOBSITE LIGHT



- Daisy chain socket
- Patented self-righting technology
- 360° light output
- 5' power cord
- Intergrated carrying handle
- Heavy-duty steel dome design
- 10,000 lumens | 120Vac 50/60Hz | 90 watts E39 mogul base

MODEL #	DESCRIPTION	BODY Style	WATTS	LAMP LIFE	LINKABLE UNITS	AMP DRAW	CORD Type	IP Rating	WEIGHT
111211	10,000 Lumen Self-Righting LED Jobsite Light	27"	90	35,000 hrs.	4	0.75A	SJTW		18 lbs.

6,000 LUMEN SELF-RIGHTING LED JOBSITE LIGHT



- · Patented self-righting technology
- 360° light output
- 5' power cord
- Intergrated carrying handle
- No hot surfaces
- 5000K color temperature
- 6,000 lumens | 120Vac 50/60Hz | 51 watts E39 mogul base

MODEL #	DESCRIPTION	BODY Style	WATTS	LAMP LIFE	LINKABLE UNITS	AMP DRAW	CORD Type	IP RATING	WEIGHT
111208	6,000 Lumen Self-Righting LED Jobsite Light	25"	51	35,000 hrs.		0.42A	SJTW		16 lbs.


WOBBLELIGHT® ACCESSORIES AND REPLACEMENT BULBS.

SPECIFICATIONS

MODEL #	DESCRIPTION	WORKS WITH
111908	85W Fluorescent Bulb	11205
111904	500W Halogen Bulb	111302
111903	400W Metal Halide Bulb	111104
111807	Nylon Reflector Shield	111203, 111204, 111205, 111206
111808	Nylon Reflector Shield	111301LED, 111303LED, 111302, 111102, 111104
111801	Replacement Reflector Dome and Cap	111302, 111102, 111104
1113186	Replacement Reflector Dome and Cap	111301LED, 111303LED
65151701	Replacement Dome and Cap	111205, 111206

*ADDITIONAL INTERNAL REPLACEMENT PARTS AVAILABLE

WOBBLELIGHT® 360° LIGHT DISTANCE



120W 360° INDUSTRIAL LIGHT



- 5000K color temperature
- Integrated cord
- 360° and 180° illumination
- 7,500 and 15,000 lumen range

SPECIFICATIONS

(ĥ	ı)
LIS	ΓED

MODEL #	MODEL # DESCRIPTION LIGHT TEMP		IP RATING	WATTS	CORD	FEATURES
111508		IP65	120W	5' - 18/3 SJTW Cord	Included: Floor Stand Tripod Mount, Hook,Two Earth Magnets	
111509	15,000 Lumens ProLight™ 360° LED Light Kit with Tripod	5,000K	IP65	120W	5' - 18/3 SJTW Cord	Included: Floor Stand Tripod Mount, Hook,Two Earth Magnets Heavy Duty Tripod
TLU-100	12,000 Lumen LED Lanterns	5,000K		100W	10' Cord	Included: Hook, Magnet, Tripod Adapter, and Paint Shield

111508

PROLIGHT™ 360° KIT FEATURES (111508 & 111509)









H00K

EARTH MAGNETS

TRIPOD

STAND

BALLOON LIGHT



9822

- Soft diffused glare-free light
- Illuminates 11,000 sq. ft.
- Rated for wet locations
- 125V

- Collapsible flame retardant fabric balloon and 9' tripod
- 15' 16/3 SJTOW cord with 5-15 plug with in-line switch
- Kit includes: tripod, LED lights head and 2 x fabric balloon covers




MODEL # DESCRIPTION		BODY STYLE	WATTS	AMPS	
ı	9822	24,000 Lumen LED Balloon Light	Tripod	200	1.62


Southwire offers a full range of overhead jobsite lighting options with an array of different light distribution models. Whether you need directional lighting or a broader distribution of light, Southwire has the perfect option for you. When considering overhead lighting, make sure to check out our Southwire Lighting Solutions; including Customized Lighting, Lighting Layout Services, and our Ready-2-Hang bulk packaging.



T60 SERIES


OPTICAL ADVANTAGE: Distributes light in all directions **WHY:** General purpose lights where wall illumination or ceiling work may be important





CL SERIES

OPTICAL ADVANTAGE: Broad distribution of light but delivers more light to the ground **WHY:** General purpose scenarios where efficient ground illumination is also a priority



INTEGRAL HOOK
FOR EASY HANGING

DAISY CHAINABLE CORDS
WITH LENGTH OPTIONS

ANGLED INTEGRAL LEDS

CL100LEDG2

T5 SERIES INTEGRATED LED OVERHEAD LIGHTS



- 5000K
- 120/277V

- 50,000 hour rated LED life
- Damp location rated
- · Rugged die-cast aluminum housing

SPECIFICATIONS



MODEL :	IODEL # DESCRIPTION V		SQ. FT. COVERAGE (AT 5 FC, HUNG AT 15FT)	AMP DRAW	FEEDTHROUGH	COLOR
T50078	8,200 Lumen Temporary Low Bay LED Light, 120/277	78W	1,600	0.65	3' - Plug Only	Copper
T50079	8,200 Lumen Temporary Low Bay LED Light, Direct Wire	78W	1,600	0.65	3' - Direct Wire	Copper

T6 SERIES INTEGRATED LED OVERHEAD LIGHTS



- 16/3 Cord
- 5000K, 80 CRI
- 50,000 hour rated LED life
- 120/277V

SPECIFICATIONS



Damp location rated



MODEL #	DESCRIPTION	WATTS	SQ. FT. COVERAGE (AT 5 FC, HUNG AT 15FT)	AMP DRAW	MAX LINKABLE UNITS	FEEDTHROUGH	COLOR
T60100	13,000 Lumen Integrated LED Cage Light	100W	2,000	0.83	7	10' - Plug and 1' - Receptacle	Copper
T60100W35	13,000 Lumen Integrated LED Cage Light	100W	2,000	0.83	5	35' - Plug and 1' - Receptacle	Copper
T60150	19,500 Lumen Integrated LED Cage Light	150W	2,646	1.25	5	10' - Plug and 1' - Receptacle	Copper
T60150W45	19,500 Lumen Integrated LED Cage Light	150W	2,646	1.25	3	45' - Plug and 1' - Receptacle	Copper

CL120 SERIES INTEGRATED LED OVERHEAD LIGHTS



- 16/3 cord
- 4800K
- 120/277V

- 50,000 hour rated LED life
- Polycarbonate lens cover
- Damp location rated

SPECIFICATIONS

c (UL) us
LISTED

MODEL #	DESCRIPTION	WATTS	SQ. FT. COVERAGE (AT 5 FC, HUNG AT 15FT)	AMP Draw	MAX LINKABLE UNITS	FEEDTHROUGH	COLOR
CL120LED	14,000 Lumen Integrated LED Cage Light, Angled LED Panel	120W	2,500	1	7	5' - Plug and receptacle	Yellow
CL120LED-W	14,000 Lumen Integrated LED Cage Light, Angled LED Panel	120W	2,500	1	7	5' - Plug and receptacle	White

LONGNECK LED TEMP CAGE LIGHT WITH PLUG & RECEPTACLE



- 5000K color temperature
- Operating temperature:
 - -40°F to 125°F
- 14/3 SJTW cord 58"
- Spring-loaded hanging clamp
- Replaceable bulb
- Lamp rated 120/277V



MODEL #	DESCRIPTION	WATTS	AMP DRAW	MAX LINKABLE UNITS
111080EC0	7,600 Lumen LED Long Neck Cage Light w/Plug and Receptacle	80W	0.8	6
1110120EC0	13,500 Lumen LED Long Neck Cage Light w/Plug and Receptacle	120W	0.9	4

1110120ECO

PREFAB LED LANTERNS



T90200

Southwire prefab lanterns come in 4 different lumen models, each model, and has a custom wiring terminal allowing you to add your own cords to fit your specific needs. When wiring, you can use the provided strain relief connectors or the ½" threaded hubs designed to fit other Southwire fittings. Each model includes a retractable handle for ceiling mounting and low-profile stacking.

- Cord-free custom wiring terminal
- Accepts 12-gauge through 16-gauge SO cord
- 1/2" threaded hub for Southwire fittings
- Accepts most sizes of Romex® Brand and MC cable when used with correct fitting
- Includes steel 2x strain relief connectors
- Retractable hanging clip for low profile
- · Made with a stackable design
- · Replaceable fixture head & wiring terminal
- 5000K CCT
- 120V 277VAC 50/60 HZ
- Custom wiring terminal block
- 2-in-1 dimmer (150W & 200W models)
- Outdoor weather rated (when used with weatherproof connectors)



T90150

SPECIFICATIONS



MODEL #	DESCRIPTION	LUMENS	HEIGHT	WIDTH	LENGTH	WEIGHT
T90060	60W PreFab LED Lantern	7,600	10.44"	6.5"	6.5"	6 lbs.
T90100	100W PreFab LED Lantern	13,700	11.44"	6.5"	6.5"	6.5 lbs.
T90150	150W PreFab LED Lantern	20,500	12.54"	6.5"	6.5"	7 lbs.
T90200	200W PreFab LED Lantern	29,500	15.88"	6.5"	6.5"	7.5 lbs.



T90100



T90060

WIRING TERMINAL



CL SERIES SECOND GEN INTEGRATED LED OVERHEAD LIGHTS



- 16/3 cord
- 5000K
- 120/277V

SPECIFICATIONS

- 50,000 hour rated LED life
- Polycarbonate lens cover
- Operating temperature: -20°F to 140°F

Damp location rated



MODEL #	DESCRIPTION	WATTS	SQ. FT. COVERAGE AT 5 FC, HUNG AT 15FT	AMP DRAW	MAX LINKABLE UNITS	FEEDTHROUGH	COLOR
CL60LED	7,200 Lumen Integrated LED Cage Light, Angled LED Panel	60W	1,320	0.5	9	5' - Plug Only	Orange
CL60LEDG2	7,200 Lumen Integrated LED Cage Light, Angled LED Panel	60W	1,320	0.5	9	6' - Plug and 1' - Receptacle	Orange
CL100LEDG2	12,000 Lumen Integrated LED Cage Light, Angled LED Panel	100W	2,000	0.83	7	6' - Plug and 1' - Receptacle	Orange
CL100LEDG2W	12,000 Lumen Integrated LED Cage Light, Angled LED Panel	100W	2,000	0.83	7	6' - Plug and 1' - Receptacle	White
CL100LED	12,00 Lumen Integrated LED Economy Cage Light	100W	2,600	1.25	7	6' - Plug and Receptacle	Orange

JOBSITE OVERHEAD LIGHTING LAYOUT SERVICES

OSHA standard 1926.56(a) requires a jobsite to have 5 foot candles of light on the ground. Southwire can help you with your lighting layout to ensure that you keep your crew safe without overspending on unnecessary lights.

Contact your Southwire sales associate for more information about Southwire's Lighting Layout Tool **EMAIL: LIGHTING@SOUTHWIRE.COM**



LET SOUTHWIRE LAYOUT YOUR JOBSITE LIGHTING

WHAT WE NEED FROM YOU

- PROJECT DIMENSIONS: Length x Width x Deck Height
- REQUESTED FOOT CANDLE LEVEL: How many foot candles do you need on your project?
- WE CAN USE YOUR DRAWINGS TO CALCULATE JOBSITE DIMENSIONS: Either .PDF or .IFC files

READY2HANG LIGHTING PROGRAM

INCREASE YOUR LIGHTING INSTALL EFFICIENCY

By reducing install time with Southwire's Ready2Hang Lighting Program.







SHIPPED COMPLETE TO YOUR JOBSITE



READY TO HANG ON YOUR JOBSITE

PROGRAM DETAILS

*Order minimum: 50+ pieces

SERVICES INCLUDES

- The Ready2Hang service does not extend lead times
- . LED bulbs come fully installed to save you time
- Assembled fixtures are removed from cardboard boxes
- Safely shipped in easily removed bubble wrap packing



REDUCE JOBSITE WASTE & CLEAN UP TIME WITH MINIMAL PRODUCT PACKAGING



ELIMINATE LIGHT FIXTURE ASSEMBLY TIME



INCREASE INSTALL SPEED WITH CUSTOM LIGHT FIXTURES



PRE-ASSEMBLED





UNPACK

WRAPPED





UNWRAP

PACKAGE





INSTALL

HANGING ACCESSORIES

Jobsites are complex. That's why it's essential to have the right product on hand to save you both time and money. Below you will find a list of Southwire products that are popular for use with our lanterns.













SC5075HF

CPMH1

JHK-32MAG

JHK-64

MCG-50A560

L-42-1

MODEL #	DESCRIPTION	FUNCTION			
	TEMPORARY LIGHTING MOUNTING ACCESSORIES				
SC-5075HF	4" Square Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications			
SC-507HFR	4" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications			
SC-507511BHF	4-11/16" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications			
CPMH1	Cage Light Fixture Hook with Threaded End	Pairs with swivel fixture hangers to provide a hanging surface for the light			
JHK-32MAG	2" J Hook with 90 lb. Magnet	Supporting and managing string light or extension cord cables			
JHK-64	2" J Hook with Mounting Hole	Supporting and managing string light or extension cord cables			
JHK-32-AB	2" J Hook with Angled Bracket with Mounting Hole	Supporting and managing string light or extension cord cables			
58299040	14" Reusable Cable Ties, Black, 15 Pack	Manage cables and hang small fixtures			
58298740	14" Reusable Cable Ties, Black, 100 Pack	Manage cables and hang small fixtures			
MCG-50A560	1/2" Cord Grip Steel	Connects and secures power supply to fixture			
	Co	NNECTORS			
BXCN50	1/2" Set Screw Connector for BX/MC Cable	Connects and secures power supply to fixture			
L-42-1	1/2" Squeeze Box Connector Straight Zinc	Connects and secures power supply to fixture			
L-41-1	1/2" Squeeze Box Connector Straight Zinc	Connects and secures power supply to fixture			
L-48-1	1/2" Flex Set Screw Box Connector Zinc	Connects and secures power supply to fixture			
MDB-50B	1/2" Double Bite Saddle Box Connector Straight Steel	Connects and secures power supply to fixture			
IML-42-1	1/2" Flex/MC/AC Straight Squeeze Box Connectors, Insulated	Connects and secures power supply to fixture			

• 6 ft.

• 10 ft.

• Other

CUSTOM LIGHT FIXTURE

CREATE THE PERFECT OVERHEAD LIGHT TO FIT YOUR LIGHTING NEEDS

We understand that each jobsite has specific needs when it comes to custom light fixtures. That's why Garvin's light fixtures can be precisely designed for each job you have.

LUMENS CORD GAUGE • 16

• 14

• 12

- 5,200
- 7,800
- 10,400
- 13,000
- 15,600
- 19,500
- 28,000







L5-15P

L7-15P

MALE CORD END	FEMALE CORD END
none	none
515P-120V 15A 3 PRONG STRAIGHT BLADE	515P-120V 15A 3 PRONG STRAIGHT BLADE
L515-120V 15A TWIST LOCK	L515-120V 15A TWIST LOCK
L520-120V 20A TWIST LOCK	L520-120V 20A TWIST LOCK
L715-277V 15A TWIST LOCK	L715-277V 15A TWIST LOCK
L720-277V 20A TWIST LOCK	L720-277V 20A TWIST LOCK



TEMPORARY LED CAGE LIGHTS



TL40LEDW



TL100LEDWS



TL200LEDWTL

- 6500K color temperature
- 50,000 hour bulb life
- · Replaceable bulbs







SPEUIFI	UAIIUIIS		5-15P	L7-15P	LISTE
MODEL #	DESCRIPTION	CORD	WATTS	VOLTS	\$
TL40LED		None	40W	120-27	7V
TL40LEDW		6' w/ 5-15P Plug	40W	120V	
TL40LEDWS	5,200 Lumen Cage Light w/ medium base LED Corncob Bulb	6' Direct Wire	40W	120-27	7V
TL40LEDWTL	DASC LED CONTCOD BUILD	6' w/ L7-15P Twist Lock Plug	40W	277V	
TL40LEDPT		1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	40W	120V	
TL60LED		None	60W	120-27	7V
TL60LEDW	1	6' w/ 5-15P Plug	60W	120V	
TL60LEDWS	7,800 Lumen Cage Light w/ medium base LED Corncob Bulb	6' Direct Wire	60W	120-27	7V
TL60LEDWTL	DUSC EED CONTCOD BUILD	6' w/ L7-15P Twist Lock Plug	60W	277V	
TL60LEDPT	1	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	60W	120V	
TL80LED		None	80W	120-27	7V
TL80LEDW	10,400 Lumen Cage Light w/ LED	6' w/ 5-15P Plug	80W	120V	
TL80LEDWS	Corncob Bulb	6' Direct Wire	80W	120-27	7V
TL80LEDWTL		6' w/ L7-15P Twist Lock Plug	80W	277V	
TL100LEDW		6' w/ 5-15P Plug	100W	120V	
TL100LEDWS	13,000 Lumen Cage Light w/ mogul	6' Direct Wire	100W	120-27	7V
TL100LEDWTL	base LED Corncob Bulb	6' w/ L7-15P Twist Lock Plug	100W	277V	
TL100LEDPT		1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	100W	120V	-
TL120LED		None	120W	120-27	7V
TL120LEDW		6' w/ 5-15P Plug	120W	120V	
TL120LEDWS	15,600 Lumen Cage Light w/ mogul base LED Corncob Bulb	6' Direct Wire	120W/120- 277V	120-27	7V
TL120LEDWTL	-	6' w/ L7-15P Twist Lock Plug	120W/277V	277V	
TL120LEDPT		1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	120W/120V	120V	
TL150LED		None	150W	120-27	7V
TL150LEDW	-	6' w/ 5-15P Plug	150W	120V	
TL150LEDWS	19,500 Lumen Cage Light w/ mogul base LED Corncob Bulb	6' Direct Wire	150W	120-27	7V
TL150LEDWTL	DASC LED CONTCOD DUID	6' w/ L7-15P Twist Lock Plug	150W	277V	
TL150LEDPT	-	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	150W	120V	
TL200LED		None	200W	120-27	7V
TL200LEDW	1	6' w/ 5-15P Plug	200W	120V	
TL200LEDWS	28,000 Lumen Cage Light w/ mogul base LED Corncob Bulb	6' Direct Wire	200W	120-27	7V
TL200LEDWTL	J DUGG ELD COTTICOD DUID	6' w/ L7-15P Twist Lock Plug	200W	277V	
TL200LEDPT	1	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	200W	120V	

TEMPORARY FLUORESCENT CAGE LIGHTS



- 105W
- 8,000 hour bulb life
- Mounting hook & steel cage

SPECIFICATIONS

(ŲL)
LISTER

MODEL #	DESCRIPTION	CORD END	VOLTS	BULB BASE
TL105CF		None	120V	Medium
TL105CFW		6' w/ 5-15P Plug	120V	Medium
TL105CFWS	6,400 Lumen, 105W	6' Direct Wire	120V	Medium
TL105CFPT	Fluorescent Temporary Light	1' cord w/ 5-15P Plug and 1' cord w/ 5-15R Receptacle	277V	Mogul
TL105CF277		None	277V	Mogul

MINI TEMPORARY CAGE LIGHTS



- Steel cage
- · Medium base

SPECIFICATIONS



MODEL #	DESCRIPTION	CORD	VOLTS
TLM		None	120V - 277V
TLMW	Mini Temporary Cage Lights	6' w/ 5-15P Plug	120V
TLMPT	willi reinporary dage Lights	6' Direct Wire	120V
TLMAGW		1' cord w/ 5-15P Plug and 1' cord w/ 5-15R Receptacle	277V

DIRECT WIRE BOX MOUNTED TEMPORARY LIGHTS



- Steel cage
- Medium bulb base
- Includes mounting plates for square and round boxes
- Direct wire



MODEL #	DESCRIPTION	BULB
TLC0	1,000 Lumen Box Mount Temp Cage Light	9W
TLMU	Box Mount Wall Sconce Temp Cage Light	

REPLACEMENT BULBS.



- 6,500K color temperature
- LED bulbs, are IP64

SPECIFICATIONS



MODEL #	DESCRIPTION	WATTS/ Volts	BULB LIFE	BULB BASE
C105651MED	6,400 Lumen, Fluorescent Bulb	105W/120V	8,000 hrs.	Medium
C105652MOG	6,400 Lumen, Fluorescent Bulb	105W/277V	8,000 hrs.	Mogul
LED036-E39	5,200 Lumen, LED Corncob Bulb	40W/120V-277V	50,000 hrs.	Medium
LED054-E39	7,800 Lumen, LED Corncob Bulb	60W/120V-277V	50,000 hrs.	Medium
LED080-E39	10,400 Lumen, LED Corncob Bulb	80W/120V-277V	50,000 hrs.	Mogul
LED100-E39	13,000 Lumen, LED Corncob Bulb	100W/120V-277V	50,000 hrs.	Mogul
LED125-E39	15,600 Lumen, LED Corncob Bulb	120W/120V-277V	50,000 hrs.	Mogul
LED150	19,500 Lumen, LED Corncob Bulb	120W/120V-277V	50,000 hrs.	Mogul
LED200	28,000 Lumen, LED Corncob Bulb	200W/120V-277V	50,000 hrs.	Mogul

HANGING ACCESSORIES







JC-100







SPECIFICATIONS

MODEL #	DESCRIPTION	FUNCTION
SC-5075HF	4" Square Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
SC-5075HFR	4" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
SC-507511BHF	4-11/16" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
CPMH1	Cage Light Fixture Hook with Threaded End	Pairs with swivel fixture hangers to provide a hanging surface for the light
JC-100	Zinc Fixture Support #12, 100'	Support light fixtures
JHK-32MAG	2" J Hook with 90 lb. Magnet	Supporting and managing string light or extension cord cables
JHK-64	2" J Hook with Mounting Hole	Supporting and managing string light or extension cord cables
JHK-32-AB	2" J Hook with Angled Bracket with Mounting Hole	Supporting and managing string light or extension cord cables
BRM200-HD	2" Bridal Rign with 90 lb. magnet	Supporting and managing string light or extension cord cables
58299040	14" Reusable Cable Ties, Black, 15 Pack	Manage cables and hang small fixtures
58298740	14" Reusable Cable Ties, Black, 100 Pack	Manage cables and hang small fixtures

CAGE LIGHT ACCESSORIES



SPECIFICATIONS

MODEL #	DESCRIPTION
TLPS	Light Pollution Shield, 13" (Works with Medium Base Fixtures)
TLPS-L	Light Pollution Shield, 15" (Works with Mogul Base Fixtures)
TLSGLK	Temp Light Lockable Acrylic Guard

TLPS

TEMPORARY HIGH BAY



17100LEDP3

- 120V/277VAC 50/60Hz
- Includes 6' power cord and 20" safety cable
- · Vibration, shock, and impact resistant
- Damp location rated

- Self-locking hook/carry handle
- M8 screw thread for easy use with tripod or eyebolt ring
- Optional tripod for quick set-up



MODEL #	DESCRIPTION	LUMENS	WATTS	SQ. FT. COVERAGE	AMP Draw	FEEDTHROUGH	COLOR
17100LEDP3	100W Temporary High Bay	12,000	100W	2,000	1A	6' - plug only	Yellow
17150LEDP3	150W Temporary High Bay	18,000	150W	2,600	1.5A	6' - plug only	Yellow

Southwire offers a full range of industrial string lights to help you light any area. Perfect for corridors and longer rooms, the majority of our string lights are available in 50 ft. & 100 ft. strands. We make sure to bring you the best in LED technology while also continuing to carry traditional E-base socket string lights. Not sure which one to choose? Provide us with your project dimensions and we'll recommend a product that works specifically for your jobsite.



LED STRING LIGHTS WITH UP-LIGHT

Shine light along hundreds of feet with ease, utilizing these convenient and easy-to-install integrated LED string lights. With no bulb to break or replace, these products are low profile and will provide service for years to come.



LED STRING LIGHT WITH REPLACEABLE HEADS

We know that string lights are often beat up, painted on, chemically damaged, or even have their cables cut. That's why we designed string lights with replaceable heads to help you keep the jobsite running smoothly — even when the unexpected happens.



100 LUMEN UPLIGHT ILLUMINATES CEILING TASKS LIKE CONDUIT AND STRUT WORK



FEATURES AN E17 BASE

REPLACEABLE HEAD ALLOWS FOR CHANGE OUT IF DAMAGED, OR TO SALVAGE PARTS IF A CABLE IS CUT



LED STRING LIGHTS WITH UP-LIGHT



7164SW

- 5000K color temperature
- IP65 heads
- 800 lumens per head

SPECIFICATIONS

- 100 lumen up-light, 700 lumen down light
- 5-15 plug and receptacle
- Mounting hole molded into top housing

(1)

MODEL #	MODEL # DESCRIPTION		CORD TYPE	HEAD COUNT	LINKABLE UNITS
7164SW	50' - 14/3, 4,000 Lumen, LED String Light	50'	14/3 SJTW	5	1,000 ft.
7165SW	100' - 14/3, 8,000 Lumen, LED String Light	100'	14/3 SJTW	10	1,000 ft.

LED STRING LIGHT - X UPLIGHT



- 2,200 lumens per head
- 120 VAC 50/60Hz
- 50ft & 100ft

- · Diffused anti-glare lens
- Heavy-duty 16/3 cord
- 4-way mounting loop

SPECIFICATIONS

ì	MODEL #	DESCRIPTION	LENGTH	CORD TYPE	HEAD COUNT	LINKABLE UNITS
	71X5SW	100' 22,000 Lumen LED String Light - X Uplight	100'	16/3 SJTW	10	5 ft.
	71X4SW	50' 11,000 Lumen LED String Light - X Uplight	50'	16/3 SJTW	5	10 ft.
	71X5SW520	100' 22,000 Lumen LED String Light - X Uplight L5-20 Twist Lock	100'	16/3 SJTW	10	5 ft.
	71X4SW520	50' 11,000 Lumen LED String Light - X Uplight L5-20 Twist Lock	50'	16/3 SJTW	5	10 ft.

LED STRING LIGHTS WITH REPLACEABLE LIGHT PANELS



- 5600K color temperature
- Removable light panel with E17 base
- 900 lumens per head

SPECIFICATIONS

- 1-15 Plug and receptacle with slide lock feature
- 50,000 hour fixture life
- Impact-resistant polycarbonate lens



97132

MODEL #	DESCRIPTION	LENGTH	CORD TYPE	HEAD COUNT	LINKABLE UNITS
97120	20' - 18/2 STW, 900 Lumen LED String Light	20'	SJTW	1	500 ft.
97135	50' - 18/2 STW, 4,500 Lumen LED String Light	50'	SJTW	5	500 ft.
97132	100' - 18/2 STW, 9,000 Lumen LED String Light	100'	SJTW	10	500 ft.

CUL US

SOCKET COUNT

5

10

PLUG & RECEPTACLE

LENGTH

STRING LIGHTS

18/3 LED COB STRING LIGHTS



- Each LED lead delivers 1,200 lumens
- Input voltage: AC 120V
- Includes hanging clip for quick hanging
- 18/3 SJTW power supply cord
- NEMA 5-15R daisy chain receptacle

SPECIFICATIONS

MODEL #	DESCRIPTION	LENGTH	CORD TYPE	HEAD COUNT	LINKABLE Units
7174SW	50' 6,000 Lumen LED String Light	50'	SJTW	5	400 ft.
7175SW	100' 12,000 Lumen LED String Light	100'	SJTW	10	400 ft.

16/3 LED STRING LIGHTS



- Each LED lead delivers 1,200 lumens
- Input voltage: AC 120V
- Includes hanging clip for quick hanging
- 18/3 SJTW power supply cord
- NEMA 5-15R daisy chain receptacle

SPECIFICATIONS

MODEL #	DESCRIPTION	LENGTH	CORD TYPE	HEAD COUNT	LINKABLE UNITS
7184SW	50' 6,000 Lumen LED String Light	50'	SJTW	5	400 ft.
7185SW	100' 12,000 Lumen LED String Light	100'	SJTW	10	400 ft.

STANDARD PLASTIC STRING LIGHTS



7145SW

- Medium base socket
- Integrated plug

MODEL #

95135

95132

- Sockets rated to 150W
- NEC compliant

JACKET

STW

12/3

12/3

• Meets OSHA requirements

CORD TYPE

• Integrated daisy chain socket (12/3 & 14/3 models only)

CAGE TYPE

SPECIFICATIONS

DESCRIPTION

50' 12/3 STW String Light, Plastic

100' 12/3 STW String Light,

Cages

Plastic Cages

7145SW	100', 14/2 SJTW String Light, Plastic Cages		14/2	Plastic	100 ft.	1-15 Only	10
7155SW	100' 14/3 SJTW String Light, Plastic Cages		14/3	Plastic	100 ft.	5-15	10
7548SW	50' 12/3 SJTW String Light, Plastic Cages	SJTW		Plastic	50 ft.	5-15	5
7549SW	100' 12/3 SJTW String Light, Plastic Cages		12/3	Plastic	100 ft.	5-15	10
96132	100' 12/3 SJTW String Light, Plastic Cages			Pre-Assembled Plastic	100 ft.	5-15	10
94132	100' 14/2 STW String Light, Plastic Cages		14/2	Pre-Assembled Plastic	100 ft.	1-15 Only	10
7146SW	100' 12/2 STW String Light,		12/2	Plastic	100 ft.	1-15 Only	10

50 ft.

100 ft.

5-15

5-15

Pre-Assembled Plastic

Pre-Assembled Plastic

STANDARD METAL STRING LIGHTS



- · Medium base socket
- Integrated plug and receptacle
- Sockets rated to 150W
- NEC compliant
- Meets OSHA requirements

SPECIFICATIONS

	US
LISTED	

MODEL #	DESCRIPTION	JACKET	CORD TYPE	CAGE TYPE	LENGTH	PLUG & RECEPTACLE	SOCKET COUNT
7538SW	50' 12/3 SJTW String Light, Metal Cages	SJTW	12/3	Metal	50 ft.	5-15	5
7539SW	100' 12/3 SJTW String Light, Metal Cages	SJIW		Metal	100 ft.	5-15	10
7599SW	100' 12/3 STW String Light, Metal Cages			Metal	100 ft.	5-15	10
95137	50' 12/3 STW String Light, Metal Cages	STW		Pre-Assembled Metal	50 ft.	5-15	5
95133	100' 12/3 STW String Light, Metal Cages			Pre-Assembled Plastic	100 ft.	5-15	10

STRING LIGHTS WITH LED BULBS.



121050

- Medium base socket
- Integrated plug
- Rough service LED bulb
- 5000K Color temperature
- NEC compliant
- Meets OSHA requirements



MODEL #	BULB LUMENS	DESCRIPTION	JACKET	CORD TYPE	CAGE TYPE	LENGTH	PLUG & RECEPTACLE	SOCKET COUNT
SLP142J100K80	800	100' 14/2 SJTW String Light with 800 Lumen Bulb, Plastic Cages	SJTW	14/2	Plastic	100 ft.	1-15 Plug Only	10
SLP143J100K80	800	100' 14/3 SJTW String Light with 800 Lumen Bulb, Plastic Cages		14/3	Plastic	100 ft.	5-15	10
1111000	1,500	100' 14/2 SJTW String Light with 1,500 Lumen Bulb, Plastic Cages	SJIW	14/2	Plastic	100 ft.	1-15 Plug Only	10
1311000	1,500	100' 14/3 SJTW String Light with 1,500 Lumen Bulb, Plastic Cages		14/3	Plastic	100 ft.	5-15	10
121050	1,500	50' 12/3 STW String Light with 1,500 Lumen Bulb, Plastic Cages	STW	12/3	Metal	50 ft.	5-15	5
1211000	1,500	100' 12/3 STW String Light with 1,500 Lumen Bulb, Plastic Cages	SIW	12/3	Metal	100 ft.	5-15	10

STANDARD TWIST-LOCK STRING LIGHTS



- Medium base socket
- L5-20 plug and receptacle
- Integrated plug and receptacle
 Sockets rated to 150W

SPECIFICATIONS





MODEL #	DESCRIPTION	JACKET	CORD TYPE	CAGE TYPE	LENGTH	PLUG & RECEPTACLE	SOCKET COUNT
SLP123J50L	50' 12/3 SJTW Locking String Light, Plastic Cages	- SJTW	Plastic	50 ft.	L5-20	5	
SLP123J100L	100' 12/3 SJTW Locking String Light, Plastic Cages	531W	12/3	Plastic	100 ft.	L5-20	10
95125	50' 12/3 SJTW Locking String Light, Plastic Cages			Pre-Assembled Plastic	50 ft.	L5-20	5
95122	100' 12/3 STW Locking String Lights, Plastic Cages	сти		Pre-Assembled Plastic	100 ft.	L5-20	10
95127	50' 12/3 STW Locking String Lights, Metal Cages	31W		Pre-Assembled Plastic	50 ft.	L5-20	5
95123	100' 12/3 STW Locking String Lights, Metal Cages			Pre-Assembled Plastic	100 ft.	L5-20	10

*UL Listed only.

STRING LIGHTS REPLACEMENT PARTS



111923

MODEL #	DESCRIPTION	WORKS WITH
72002000	Metal Replacement Cage	All standard string light models
73010000	Plastic Replacement Cage	All standard string light models
9700	Replacement Magnetic Yolk	91135, 91120
9709	E17 Replacement Light Panel	97120, 97135, 97132
9711	E26 Replacement Light Panel	97132, 97135
105WCFL	Compact Fluorescent, 105W	All standard string light models
23WCFL	Compact Fluorescent, 23W	All standard string light models
111919	800 Lumen LED Medium Base Bulb	All standard string light models
111923	1,500 Lumen LED Medium Base Bulb	All standard string light models

CART LIGHTS

Southwire offers many high lumen cart lights to make sure any job can be well lit while still giving you the option to move lights around the jobsite easily and effortlessly. Whether you need 11,000 lumens or 44,000 lumens, Southwire has you covered. We also understand that some jobs are still using halogen cart lights so we have made sure to continue to bring you a great halogen cart light option that has stood the test of time.



CART LIGHTS

7000 SERIES LED CART LIGHT



- 125V
- 12' 18/3 SJTW power cord 5-15
- Self-breaking wench 7322

SPECIFICATIONS

- Adjustable head with protective wire cages
- · Steel cart base
- Wet locations



MODEL #	DESCRIPTION	LUMENS	MAST HEIGHT	HANDLE/ MAST STYLE	HEAD COUNT	TOTAL WATTS	AMPS
7309	22,000 Lumen, Single Head, 2 Stage Cart Light	22,000	5 ft 10 ft.	2 Stage Mast	1	200W	1.7A
7322	44,000 Lumen, Dual Head, 2 Stage Winch Cart Light	44,000	5.5 ft 12 ft.	2 Stage with 600 lbs Winch	2	400W	2.14A
ACCESSORIES							
7300HA	Replacement Head for 7309	22,000					
7300DHA	Replacement Head for 7322	44,000					

9000 SERIES LED CART LIGHT



- 12' 18/3 SJTW power cord 5-15

- Adjustable head with protective wire cages
- · Steel cart base
- Wet locations



MODEL #	DESCRIPTION	LUMENS	MAST HEIGHT	HANDLE/ MAST STYLE	HEAD COUNT	TOTAL Watts	AMPS
9842	11,000 Lumen, Twin Head, 2 Stage Cart Light	11,000	5 ft 10 ft.	2 Stage Mast	2	100W	0.8A
9322	44,000 Lumen, Quad Head, 2 Stage Winch Cart Light	22,000	5.5 ft 12 ft.	2 Stage Mast with 600 lbs. Winch	4	200W	1.6A
ACCESSORIES							
9800DHA	Replacement Head for 9842	11,000					
9900DHA	Replacement Head for 9322	22,000					

WORK LIGHTS

From LED to halogen, rechargeable to corded, we've got a work light for almost any situation. Many of our work lights carry high IP ratings, with weather-resistant ratings, and some even being submersible in water. If durability and power are what you're looking for in a work light then Southwire will be able to satisfy your needs.



WORK LIGHTS

RECHARGEABLE FOLDING WORK LIGHT

LIGHT WINGS FOLD TO PROVIDE ILLUMINATION UP TO 360°

C/EP ONETRICTOR OLD THE PRODUCT OF T

BATTERY WITH 2 HOUR RUN TIME

BATTERY LIFE INDICATOR AND 2 MODE SETTINGS (2,000 & 4,000 LUMENS)

LIGHT WINGS FOLD OVER TO PROTECT LED LENS WHEN NOT IN USE

RECEPTACLE FOR DAISY CHAINING MULTIPLE LIGHTS



AVAILABLE WITH TRIPOD

WORK LIGHTS

AL SERIES RECHARGEABLE AND CORDED WORK LIGHTS

For the serious tradesman, Southwire's AL series work light is packed with features and is built to last.





CORDED 6,000 AND 10,000 LUMEN MODELS RECHARGEABLE 2,000 AND 6,000 LUMEN MODELS

APP ENABLED, CONTROL MULTIPLE LIGHTS
FROM THE SAME APP (AVAILABLE ON THE 6,000
AND 10,000 LUMEN MODELS)



SLIM SERIES LED WORK LIGHT



- Aluminum body
- IP65, indoor or outdoor use
- Operating temp: -40°F to 122°F
- 5000K LED with 50,000 hrs. life
- 120V, 5' 18/3 SJTW cord

SPECIFICATIONS



MODEL #	DESCRIPTION	LUMENS	WATTS	STAND
411015	1,500 Lumen LED Slim Work Light	1,500	15W	Floor Stand
411215	1,500 Lumen LED Slim Work Light w/ Tripod	1,500	15W	Tripod
411315	3,000 Lumen LED Twin Head Slim Light w/ Tripod	1,500 x2	30W	Tripod
411030	3,000 Lumen LED Slim Work Light	3,000	30W	Floor Stand
411430	3,000 Lumen LED Slim Work Light w/ Magnetic Base	3,000	30W	Magnetic Disc Base
411230	3,000 Lumen LED Slim Work Light w/ Tripod	3,000	30W	Tripod
411330	6,000 Lumen LED Twin Head Slim Light w/ Tripod	3,000 x2	60W	Tripod
411050	5,000 Lumen LED Slim Work Light	5,000	50W	Floor Stand
411450	5,000 Lumen LED Slim Work Light w/ Magnetic Base	5,000	50W	Magnetic Disc Base
411250	5,000 Lumen LED Slim Work Light w/ Tripod	5,000	50W	Tripod
411350	10,000 Lumen LED Twin Head Slim Light w/ Tripod	5,000 x2	100W	Tripod

AL SERIES HEAVY DUTY WORK LIGHT



411350

- IP67 submersible in water
- Impact-resistent die-cast housing, drop tested to 1M
- USB power outlet for charging other devices
- 3-year warranty

- Dimmable
- Bluetooth® control via app available in Apple and Android store
- Dual power system: can run on charge or while plugged in



MODEL #	DESCRIPTION	LUMENS	WATTS	STAND
AL100CSW	10,000 Lumen LED Work Light	10,000	100W	Magnetic Swivel Stand
AL60CSW	6,000 Lumen LED Work Light	6000	60W	Magnetic Swivel Stand

9000 SERIES HEAVY DUTY LED WORK LIGHT



9125

- 50,000 hour rated LED
- 5000K color temperature
- 120V
- · All-steel stand and tripod
- · Rated for wet locations
- Impact-resistant poly carbonate lens
- Replacement lenses available to cover paint and chemical over spray

LUMENS


5,500

5,500

5,500







PROLIGHT™ XLE SERIES LED HEAVY DUTY WORK LIGHT



- IP65 indoor or outdoor use
- Operating temp: -30°F to 120°F
- 5000K LED with 50,000 hrs. life
- Aluminum body, tempered glass, and protective cage

HEAD COUNT

1

1

1

WATTS

50W

50W

50W

STAND

Roll Cage

Floor Stand & Magnet

19" DIA - 2 Stage Tripod

• 120V, 5' - 18/3 SJTW cord

SPECIFICATIONS



MODEL #	DESCRIPTION	LUMENS	WATTS	STAND
111500	6.500 Lumen LED PROLIGHT™ Work Light w/ Floor Stand	6,500	50W	Floor Stand
111505	6,500 Lumen LED PROLIGHT™ Work Light w/ Tripod	6,500	50W	Tripod
111507	6.500 Lumen LED PROLIGHT™ Work Light w/ Magnet	6,500	50W	Magnet
111000	13,000 Lumen LED PROLIGHT™ Twin Head Work Light	6,500 x2	100W	Dual Head w/ Tripod
111005	13,000 Lumen LED PROLIGHT™ Twin Head Work Light w/ Tripod	6,500 x2	100W	Dual Head w/ Tripod

RATCHETING LED WORK LIGHTS



- On/Off switch
 - 18/3 SJTW cord

360° rotating head

5000K color temperature

. Multi-position ratcheteing floor stand

MODEL #	DESCRIPTION	LUMENS	HEIGHT	WIDTH	LENGTH	WEIGHT
CSW1X1	1500 Lumen Ratcheting LED Work Light	1,500	26"	7"	24.5"	2.7 lbs.
CSW3X1	3000 Lumen Ratcheting LED Work Light	3,000	26"	7"	24.5"	2.7 lbs.
CSW5X1	5000 Lumen Ratcheting LED Work Light	5,000	28"	8"	26.5"	3.7 lbs.
CSW10X1	10000 Lumen Ratcheting LED Work Light	10,000	31.5"	9"	31.5"	4.7 lbs.

WING LIGHTS



9220

- Rotating panel design allows for 180° to 360° illumination
- 5000K color temperature
- 120V
- · All-steel stand and tripod

- Suitable for wet locations
- Impact-resistant polycarbonate lens
- · Replacement lenses available to cover paint and chemical over spray



SPECIFICATIONS

MODEL #	DESCRIPTION	LUMENS	WATTS	STAND
9220	8,000 Lumen LED Wing Style Work Light on Tripod	8.000	80W	H-Stand
9270	8,000 Lumen LED Wing Style Work Light on Tripod	8,000	0011	Tripod

DUAL HEAD LED WORK LIGHTS



- Includes: 2-step tripod stand
- · Quick-release dual head base
- On/Off switch
- 18/3 SJTW cord

- 5000K color temperature
- CSW3X2: Each head delivers 3000 lumens
- CSW5X2: Each head delivers 5000 lumens
- CSW10X2: Each head delivers 10000 lumens

MODEL #	DESCRIPTION	LUMENS	HEIGHT	WIDTH	LENGTH	WEIGHT
CSW3X2	6000 Lumen Dual Head Work Light with Tripod	6,000	48.5"	16"	21"	9.4 lbs.
CSW5X2	10000 Lumen Dual Head Work Light with Tripod	10,000	62.5"	16"	24"	12.4 lbs.
CSW10X2	20000 Lumen Dual Head Work Light with Tripod	20,000	68"	16"	24"	14.9 lbs.

HALOGEN WORK LIGHTS





MODEL #	DESCRIPTION	WATTS	HEAD COUNT	STAND
L878	Halogen Work Light with 4-in-1 Mounting Kit	250W	1	4-in-1, Curved Tube Stand, clamp, ground stake, hanging hook
L860	Halogen Work Light	250W	1	Curved Tube Stand
L20	Halogen Work Light with Plastic Handle	500W	1	Curved Tube Stand
L33	Halogen Work Light with Metal Handle	500W	1	Curved Tube Stand
5125ITL	Halogen Work Light with Twist Lock Plug	500W	1	Curved Tube Stand
L10SLED	Halogen Work Light with Tripod and Detachable H-Stand	500W	1	Tripod and Detachable H-Stand
L13	Halogen Twin Head Work Light with Tripod	1,000W	2	Tripod
L14SLED	Halogen Twin Head Work Light with Tripod and Detachable Sled	1,000W	2	Tripod and Detachable Sled





RECHARGEABLE LED FOLDING WORK LIGHT



- Integrated lithium ion battery 7.4V, 800 mAh
- IP65, indoor or outdoor use
- 50,000 hour LED life

- Operating temp: -10°F to 125°F
- 5000K light temperature

SPECIFICATIONS

MODEL #	DESCRIPTION	ACCESSORIES	LUMENS	WATTS	RUN TIME	RECHARGE TIME
514124	PROLIGHT™ Folding LED Work Light	Wall Charger Car Charger	2,400 LM - High		2.5 hrs High	
514125	PROLIGHT™ Folding LED Work Light	Wall Charger Car Charger Tripod	1,200 LM - High 1,200 LM - Med 800 LM - Low	30W	5 hrs Medium 8 hrs Low	4 hrs.

RECHARGEABLE AL SERIES LED WORK LIGHTS



AL60RSW

- IP67 submersible in water
- Impact-resistent die-cast housing
- Drop tested to 1M

SPECIFICATIONS

- USB Power outlet for charging other devices
- 3-year warranty
- . Dimming capability
- Bluetooth® control via app available in Apple and Android store - AL60RSW only
- · Dual-power system



RECHARGE MODEL # DESCRIPTION LUMENS **RUN TIME** WATTS STAND 2.5 hrs. - 15 AL20RSW 20W 2,000 Lumen LED Rechargeable Work Light 2,000 5 hrs. Magnetic Swivel Stand hrs AL60RSW 6,000 Lumen LED Rechargeable Work Light 6.000 1 hrs. - 6 hrs. 60W 8 hrs. Swivel Stand

RECHARGEABLE LED WING LIGHT



- Rotating panel design allows for 180° to 360° illumination
- High and low output settings
- · Battery indicator shows remaining power
- Rated for wet locations
- Receptacle on back allows for daisy chaining more lights or running other small products

SPECIFICATIONS




MODEL#	DESCRIPTION	LUMENS	WATTS	RUN TIME	RECHARGE TIME	STAND
7270	4,000 Lumen LED Wing Style Rechargeable Work Light on Tripod	4.000	51W	2 hrs 4	6 hrs.	Tripod
7220	4.000 Lumen LED Wing Style Rechargeable Work Light on H-Stand	4,000	SIW	hrs.	U III S.	H-Stand

YELLOW JACKET® RECHARGEABLE CLAMP WORK LIGHT



- . Unique clamping base
- · 2-Axis swiveling head for directing light
- IP54 water resistant

- Battery level indicator
- High and low output settings
- 5000K color temperature



TRIPODS



SPECIFICATIONS

MODEL #	DESCRIPTION	MAX HEIGHT	WEIGHT	WORKS WITH
311001	Standard Tripod	5'	7.5 lbs.	411215, 511510, 514124, 514125, 516001, 516002, 516003, 516004
311006	Medium Duty Tripod	5'	8.5 lbs.	411315, 411230, 411330, 411250, 411350, 111505, 515100, 515103, 515104
311007	Heavy Duty Tripod	6'	9.5 lbs.	111005, 111508, 111509

HALOGEN REPLACEMENT BULBS





MODEL #	DESCRIPTION	WATTS	BULB QUANTITY
5911	T3 Halogen Bulb	150W	1
L21	T3 Halogen Bulb in Plastic Storage Case, 6 Pack	250W	6
L96	T3 Halogen Bulb	250W	1
L22	T3 Halogen Bulb in Plastic Storage Case, 6 Pack	300W	6
L12500W	T3 Halogen Bulb in Plastic Storage Case, 3 Pack	500W	3
L16	T3 Halogen Bulb	500W	1
L23	T3 Rough Service Halogen Bulb in Plastic Storage Case, 6 Pack	500W	6
78805000SW	T3 Halogen Bulb, 50 Pack	500W	50
L15	T3 Halogen Bulb in Plastic Storage Case, 6 Pack	600W	6

PERSONAL LIGHTING

Southwire offers a unique range of personal and handheld lighting from headlamps to rechargeable handheld lights. The entire range is loaded with unique features that will bring you ease in any situation you encounter. When buying a Southwire Personal Light, make sure to review our IP ratings and battery runtimes, as we've built them to meet the harsh demands of the jobsite.



PERSONAL LIGHTING

ALKALINE BATTERY HEAD LAMP



HL1030SW

- · Foam forehead pad
- · Adjustable elastic head band
- · Smooth dimming

- Hinged aimable head
- 2 x AAA batteries included

SPECIFICATIONS

MODEL #	DESCRIPTION	SPOT LIGHT LUMENS	FLOOD LIGHT LUMENS	RUN TIME	BATTERIES INCLUDED
HL1030SW	300 Lumen LED Adjustable Headlamp with (2x) AAA	120	300 - High 30 - Low	Up to 30 hrs.	2 x AAA Batteries

RECHARGEABLE HEAD LAMPS



HL12RSW

- Detachable magnetic light head
- Constant current maintains light level throughout the life of the charge
- IP65 weatherproof
- 3-year warranty
- Lithium ion battery

- HL25RSW has a hands free on/off sensor and down light for near field tasks like reading
- · Includes two hard hat clips and charger



HL25RSW

SPECIFICATIONS

MODEL #	DESCRIPTION	DOWN LIGHT LUMENS	SPOT LIGHT LUMENS	FLOOD LIGHT Lumens	RUN TIME	RECHARGE TIME
HL12RSW	HL12RSW 120 Lumen Rechargeable LED Head Lamp		N/A	120 - High 60 - Low	Up to 5 hrs.	2-3 hrs.
HL25RSW	250 Lumen Rechargeable LED Head Lamp	120 - High, 60 - Low	150	250 - High 75 - Low	Up to 8 hrs.	2-3 hrs.

SL SERIES RECHARGEABLE HAND HELD LIGHTS



- Magnetic base
- Hanging hook
- Articulating arm
- Spot light tip
- 1M drop test
- Includes carrying case
- Constant current maintains light level throughout the life of the charge
- 3-year warranty
- Lithium ion battery

SPECIFICATIONS

MODEL #	DESCRIPTION	SPOT LIGHT LUMENS	FLOOD LIGHT LUMENS	RUN TIME	CHARGER INCLUDED
SL20RSW	200 Lumen Rechargeable Folding LED Handheld Light	100	200 - High 50 - Low	Up to 10 hrs.	Yes
SL50RSW	500 Lumen Rechargeable Folding LED Handheld Light	100	500 - High 100 - Low	Up to 12.5 hrs.	Yes

SL20RSW SL50RSW

PERSONAL LIGHTING

YELLOW JACKET® H SERIES RECHARGEABLE HAND HELD LIGHTS



HHL1030R

HHL1060R

- Magnetic swivel base
- · Smooth dimming
- Hanging hook

- 6000K color temperature
- Lithium ion battery
- Spot light on tip (HHL1040R and HHL1060R)

SPECIFICATIONS

MODEL #	DESCRIPTION	SPOT LIGHT LUMENS	FLOOD LIGHT LUMENS	RUN TIME	CHARGER INCLUDED
HHL1030R	200 Lumen Yellow Jacket Rechargeable LED Pocket Light	NA	300 - High 30 - Low	Up to 10 hrs.	Yes
HHL1040R	HHL1040R 400 Lumen Yellow Jacket Rechargeable LED Hand Held Adjustable Light		400 - High 40 - Low	Up to 10 hrs.	Yes
HHL1060R 600 Lumen Yellow Jacket Rechargeable LED Hand Held Adjustable Light		150	600 - High 60 - Low	Up to 15 hrs.	Yes

WOODS® ALKALINE BATTERY HAND HELD LIGHT



TLB20020

- Magnetic swivel base
- Spot light in end of light
- · Swivel hanging hook

MODEL #	DESCRIPTION	LUMENS	BATTERY TYPE	
TLB20020	200 Lumen Handheld Task Light, w/ 3x AA Batteries	200	3x AA Batteries	

CLAMP & TROUBLE LIGHTS

Southwire's line of trouble lights and clamp lights are extensive to fit any need you might have. These trouble lights come in medium or heavy-duty styles, each with multiple variants to fit your specific needs, while Southwire clamp lights come in a wide range of wattage and reflector sizes.



CLAMP & TROUBLE LIGHTS

MEDIUM DUTY TROUBLE LIGHTS



SPECIFICATIONS



MODEL #	DESCRIPTION	CORD LENGTH	CORD	JACKET	OUTLET	GUARD
200	Medium Duty 15' Plastic Trouble Light, 18/2	15'	18/2		No	Plastic
201	Medium Duty 25' Plastic Trouble Light, 18/2	25'	18/2	SJTW	No	Plastic
681	Medium Duty 25' Metal Trouble Light, 18/3 w/ Outlet	25'	18/3		Yes	Metal
682	Medium Duty 50' Metal Trouble Light, 18/3 w/ Outlet	50'	18/3		Yes	Metal
691	Medium Duty 50' Metal Trouble Light, 16/3 w/ Outlet	25'	16/3		Yes	Metal
692	Medium Duty 50' Metal Trouble Light, 16/3 w/ Outlet	50'	16/3	1	Yes	Metal
48000	Metal Cord Reel, 40' Metal Trouble Light w/ Outlet	40'	16/3		Yes	Metal

HEAVY DUTY TROUBLE LIGHTS



- Durable oil-resistant cord jacket
- Elastomer cord jacket allows for maximum flexibility



MODEL #	DESCRIPTION	CORD LENGTH	CORD	JACKET	OUTLET	GUARD
56578802SW	Heavy Duty Trouble Light, 16/3, 25' SJEOW, Metal Guard, w/ Outlet	25'	10/0		Yes	Metal
56588802SW	Heavy Duty Trouble Light, 16/3, 50' SJEOW, Metal Guard, w/ Outlet 50'		16/3	- SJEOW	Yes	Metal
58578802SW	Heavy Duty Trouble Light, 14/3, 25' SJEOW, Metal Guard, w/ Outlet	25'	14/0	SJEOW	Yes	Metal
58588802SW	Heavy Duty Trouble Light, 14/3, 50' SJEOW, Metal Guard, w/ Outlet		14/3		Yes	Metal

CLAMP & TROUBLE LIGHTS

STEEL CLAMP LIGHTS



160

- Non-marring clamp grip
- Built-in hook
- 18/2 cord

- Porcelain socket
- Steel clamp
- Push-through switch

SPECIFICATIONS

(ŲL)
LISTED

MODEL #	DESCRIPTION	WATTS	CORD	REFLECTOR DIA	BULB PROTECTOR
160	60W Clamp Light with 5.5" Reflector	60W	6' SJTW	5.5"	No
324	125W Clamp Light with Wire Reflector	125W	6' SJTW	Wire	No
328	150W Clamp Light with None Reflector	150W	6' SJTW	None	No
151	150W Clamp Light with 8.5" Reflector	150W	6' SJTW	8.5"	No
2839	150W Clamp Light Socket with No Reflector	150W	12' SJTW	8.5	No
162	150W Clamp Light with 10" Reflector	150W	6' SJTW	10"	No
165	250W Clamp Light with 10.5" Reflector	250W	6' SJTW	10.5"	Yes
166	300W Clamp Light with 10" Reflector	300W	6' SJTW	10"	Yes
167	300W Clamp Light with 10.5" Reflector	300W	8' SJTW	10.5"	Yes

LED CLAMP LIGHT



- Non-marring clamp grip
- 18/2 cord

	•
Intertek	

MODEL #	DESCRIPTION	CORD
CL20600YJ	600 Lumen LED Clamp Light	6' SJTW

INSTALLED LIGHTS

Southwire's installed lights cover a wide range of uses from durable steel-armed dock lights to powerful security and dusk to dawn lights, to weathertight utility lights. We have made sure to provide you with high-output LED options as well as traditional bulb products.



SECURITY LIGHTS

CUL US

INSTALLED LIGHTS

DOCK LIGHTS



- 40" Reach
- IP65 weatherproof (111510 and 111515)
- Durable steel arm that prevent sagging
- Integrated power cord with plug

SPECIFICATIONS

MODEL #	DESCRIPTION	LUMENS	WATT	LIGHT Source	LIGHT COLOR TEMPERATURE	BULB LIFE	FEATURES	CERTIFICATION
111510	LED Dock Light			Intograted		50.000		
111515	Replacement LED Dock Light Head	1,700	20W	Integrated LED	5000K	hrs.	IP65	cUL

120V SECURITY LIGHTS WITH BULBS.



				maic
MODEL #	DESCRIPTION	LAMP TYPE	WATT	PHOTOCELL INCLUDED
L1701	100W Metal Halide Dusk to Dawn Security Light	Metal Halide	100	Yes
L1755	65W Mogul Base Fluorescent Security Light	Mogul Fluorescent	65	No
L1730	70W High Pressure Sodium Dusk to Dawn Security Light	Metal Halide	150	Yes
L1741	150W High Pressure Sodium Dusk to Dawn Security Light	High Dragoura Codium	150	Yes
L177070W	70W High Pressure Sodium Dusk to Dawn Wall Light	High Pressure Sodium	70	Yes

INSTALLED LIGHTS

SECURITY LIGHTS



32W MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 180° Motion detection with up to 45' range
- 2-head LED light fixture
- Polycarbonate lens
- Delay time: test/1min/5min/10min
- 3,200 lumens | 120Vac | 32 watts
- 6000K color temperature



L17SL303MW

34W MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 240° Motion detection with up to 45' range
- 3-head LED light fixture
- · Polycarbonate lens
- Delay time: test/1min/5min/10min
- 3,800 lumens | 120Vac | 34 watts
- 6000K color temperature



L17S0L183MW

240-DEGREE SOLAR MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 240° Motion detection with up to 45' range
- 3-head LED light fixture
- · Polycarbonate lens
- Delay time: test/30s/60s/120s
- 1,800 lumens | solar | 2000mAh li-ion battery
- 6000K color temperature



MODEL #	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
L17SL252MW	32W Motion Activated White LED Security Light	6.5"	7.1"	7.7"	2.4 lbs.
L17SL303MW	34W Motion Activated White LED Security Light	6.5"	7.9"	9.6"	3.2 lbs.
L17S0L183MW	240-Degree Solar Motion Activated White LED Security Light	6.9"	8.3"	9.4"	3.4 lbs.

BARN LIGHTS

INSTALLED LIGHTS

DUSK TO DAWN BARN LIGHTS




L17BL1036

35W DUSK TO DAWN LED BARN LIGHT

- · Intergrated photocell sensor
- Bronze aluminum housing
- Frosted polycarbonate lens
- Suitable for wet locations
- 3,675 lumens | 35 watts
- 5000K color temperature
- 120-277Vac 50/60Hz

42W DUSK TO DAWN LED BARN LIGHT



- · Bronze aluminum housing
- Frosted polycarbonate lens
- · Suitable for wet locations
- 5,000 lumens | 42 watts
- 5000K color temperature
- 120-277Vac 50/60Hz

L17BL2050

L17BL2065

58W DUSK TO DAWN LED BARN LIGHT

- Intergrated photocell sensor
- Bronze aluminum housing
- Frosted polycarbonate lens
- · Suitable for wetlocations
- 7,000 lumens | 58 watts
- 5000K color temperature
- 120-277Vac 50/60Hz



MODEL #	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
L17BL1036	35W Dusk to Dawn LED Barn Light	5.5"	6.5"	10.3"	1.8 lbs.
L17BL2050	42W Dusk to Dawn LED Barn Light	5.2"	10"	13.8"	3.4 lbs.
L17BL2065	58W Dusk to Dawn LED Barn Light	5.5"	10"	13.8"	3.4 lbs.


INSTALLED LIGHTS

WEATHER TIGHT UTILITY LIGHTS



I 1706

SPECIFICATIONS



LED or incandescent bulbs.

- Durable cast-aluminum housing
- Tempered safety glass



MODEL #	DESCRIPTION	MOUNT	COLOR
L1706			Gray
L1706AB		Ceiling Mount	Antique Brass
L1706BLK	150W Outdoor Weather Tight Ceiling Mount Utility Light		Black
L1706BS			Brushed Steel
L1706CH			Chrome
L1707SV			Gray
L1707SVAB	150W Outdoor Woother Tight Wall Mount Hillity Light	Wall Mount	Antique Brass
L1707SVBLK	- 150W Outdoor Weather Tight Wall Mount Utility Light		Black
L1707SVBS			Brushed Steel

DUSK TO DAWN PHOTO CONTROLS



L1707SV

L4700WD

- · Automatically turns lights on at dusk and off at dawn
- Compatible with incandescent, fluorescent, halogen, LED, mercury vapor, high pressure sodium twist lock also compatible with metal halide
- Time delay eliminates flicker and false On/Off triggers

SPECIFICATIONS



MODEL #	DESCRIPTION	CONNECTION	FEATURE	ELECTRICAL SPECIFICATIONS
59408WD	Post Eye Light Control	HARDWIRE	HD Bi-metal Switch	120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 5A Electronic Ballast
59410WD	Stem Mount Light Control	HARDWIRE	Light Level Adjust	120Vac 60Hz, 2000W Tungsten, 2000VA Magnetic Ballast, 15A Electronic Ballast
59411WD	Stem and Swivel Light Control	HARDWIRE	Adjustable	120Vac 60Hz, 2000W Tungsten, 2000VA Magnetic Ballast, 15A Electronic Ballast
59413WD	Swivel Mount Light Control	HARDWIRE	Light Level Adjust	120Vac 60Hz, 1800W Tungsten, 1100VA Magnetic Ballast, 3A Electronic Ballast
59412WD	Heavy Duty Twistlock Light Control	TWIST LOCK	Surge Protection	110-277Vac 60Hz, 1800W Tungsten, 1000VA Magnetic Ballast, 5A Electronic Ballast
L4700WD	Twist Lock Light Control	TWIST LOCK	Surge Protection	120Vac 60Hz, 1800W Tungsten, 1100VA Magnetic Ballast, 5A Electronic Ballast

OUTDOOR TIMER SWITCHES



59103RWD

- Ideal use for lighting, signs, pumps, compressors, and other heavy duty application
- Manual override switch
- NEMA 3R lockable box

- 1/2" and 3/4" knockouts
- 48 On/Off settings, 30 minute intervals, repeats daily



	MODEL #	DESCRIPTION	TYPE	SPECIFICATIONS
ſ	59101RWD	24hr Heavy Duty Mechanical Time Switch	SPST	120Vac, 60Hz, 40A General/Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 2HP (24FLA)
	59103RWD	24hr Heavy Duty Mechanical Time Switch	DPST	120Vac, 60Hz, 40A General/Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 2Hp (24FLA)
	59104RWD	24hr Heavy Duty Mechanical Time Switch	DPST	208-277Vac, 60Hz, 40A General/Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 2Hp (24FLA)

HAZARDOUS LOCATION LIGHTING

Southwire carries a range of hazardous location rated drop and inspection lights that allow you to safely light a hazardous location.



HAZARDOUS LOCATION

HAZARDOUS LOCATION LED LIGHTS



514009

- Lithium ion battery
- For use in hazardous areas
- Impact-resistant construction



MODEL #	DESCRIPTION	LUMENS	RUN TIME	BATTERY TYPE	IP RATING	FEATURE
514007	125 Lumen Intrinsically Safe LED Flashlight	125 LM - High 55 LM - Low	42.5 Hrs High 80 Hrs Low	x3 C	IP67	Waterproof
514008	160 Lumen Intrinsically Safe LED Flashlight	160 LM - High 65 LM - Low	6 Hrs High 13 Hrs Low	x4 AA	IP67	Waterproof
514009	270 Lumen Intrinsically Safe Right Angle LED Flashlight	270 LM - High 135 LM - Low	6.5 Hrs High 13 Hrs Low	x4 AA	IP54	Waterproof
514012	200 Lumen Intrinsically Safe LED Head Lamp	200 LM - High 100 LM - Low	2.5 Hrs High 4.5 Hrs Low	x3 AAA	IP67	Waterproof

NOTES





/SOUTHWIRETOOLS



/SOUTHWIRE-COMPANY



@SOUTHWIRETOOLS



@SOUTHWIRE



WWW.SOUTHWIRE.COM | 1-855-SWTOOLS

All Trademarks or Registered Trademarks (TM/e) are owned or licensed by Southwire Company. Any other $^{\text{TM}}/\textcircled{e}$ - Trademark or Registered Trademark of Southwire Company.