



TECK 90 SPECIFICATIONS CSA TECK 90 – 1000V CONTROL CABLE

SPECIFICATIONS

Stock Number	Conductor		Grounding Conductor Size	Approximate Diameter			Approximate Weight	Ampacity (Amps) 30°C Ambient †	
				Inner Jacket	Armour	Outer Jacket		75°C	90°C
	Size AWG	Number of Conductors	AWG	inches	inches	inches	lb/1000 ft		
**	14	2	14	0.421	0.646	0.746	218	20	25
56352299	14	3	14	0.434	0.650	0.757	235	20	25
56844899	14	4	14	0.475	0.685	0.769	267	20	25
56712199	12	2	12	0.444	0.654	0.738	237	25	30
56352699	12	3	12	0.473	0.683	0.767	273	25	30
**	12	4	12	0.560	0.775	0.865	346	25	30
58200399	10	2	12	0.491	0.687	0.801	297	35	40
56229799	10	3	12	0.554	0.764	0.848	358	35	40
56861199	10	4	12	0.605	0.815	0.899	416	35	40

** Non-stock item - special order required

† Ampacities based on not more than 3 conductors (4 with neutral) in raceway or cable as per Table 2 of 2015 Canadian Electrical Code