




TelcoFlex® TELECOM POWER

THE TRUSTED CHOICE.

Southwire telecom power products are among the premier LSZH central office DC & AC power cables in the industry. Our TelcoFlex® cables power all levels of telecom equipment and battery backup systems used in the central office, CATV head-end, data center, and cell tower equipment shelter environments.



Why Southwire for Telecom Power?

Industry Compliant: TelcoFlex® products have surpassed all 33 Telcordia Technologies test requirements, met ATIS certification, and all other industry standards.

TelcoHyde® Insulation: TelcoFlex® products feature TelcoHyde® insulation, a non-halogen, low smoke, environmentally friendly non-silicone, lead-free thermoset rubber compound that helps provide protection to your critical data equipment in the event of a fire.

Flexibility & Durability: TelcoFlex® cables offer increased flexibility and durability for better cable pulling through trays.

Our Authorized Channel Partners: GCG, Talley, and Wesco provide regional distribution centers to deliver what you need, when you need it.




TALLEY



Proven History: Installers have been using TelcoFlex® cables on their jobs for over 30 years. Southwire continues to build upon a 70+ year history of innovating to meet customers' needs.

FOR MORE INFORMATION CONTACT TELCOFLEX@SOUTHWIRE.COM



**SCAN TO
LEARN
MORE**



**WE'VE GOT IT
MADE IN AMERICA™**



Southwire®

TelcoFlex® L2 Telecom Power



SIZE	STRANDING	NOMINAL CONDUCTOR DIAMETER (INCHES)	INSUL. MIN. AVG. WALL (MILS)	NOMINAL INSUL. DIAM. (INCHES)	MAX D.C. RES @ 20°C (OHMS/MFT)	APPROX. WEIGHT (lb/1000ft)	AMPACITY PER NEC TABLE 310.15(B)(16)	
							75°C	90°C
14	41	.077	45	.170	2.730	24	20	25
12	65	.089	45	.182	1.720	35	25	30
10	104	.116	45	.209	1.080	50	35	40
8	41	.153	60	.280	0.679	78	50	55
6	65	.186	60	.315	0.436	122	65	75
4	126	.260	60	.365	0.274	205	65	95
2	168	.305	60	.430	0.172	254	115	130
1	210	.370	80	.540	0.126	351	130	150
1/0	266	.392	80	.560	0.109	420	150	170
2/0	342	.455	80	.620	0.057	536	175	195
4/0	532	.577	80	.745	0.055	792	230	260
350	888	.760	95	.960	0.033	1250	310	350
500	1221	.890	95	1.090	0.023	1713	380	430
750	1850	1.094	110	1.320	0.016	2682	475	535

Available in colors: gray, green, red, blue, black, red with black stripe, blue with black stripe, and gray with black stripe

TelcoFlex® L3 Telecom Power Wire



SIZE	STRANDING	NOMINAL CONDUCTOR DIAMETER (INCHES)	INSUL. MIN. AVG. WALL (MILS)	NOMINAL INSUL. DIAM. (INCHES)	MAX D.C. RES @ 20°C (OHMS/MFT)	APPROX. WEIGHT (lb/1000ft)	AMPACITY PER NEC TABLE 310.15(B)(16)	
							75°C	90°C
14	7	.0708	45	.164	.226	36	20	25
12	7	.0892	45	.182	.244	46	25	30
10	7	.1130	45	.210	.272	62	35	40
8	7	.1420	60	.265	.327	93	50	55
6	7	.1780	60	.304	.370	132	65	75
4	7	.2250	60	.348	.414	188	85	95
2	7	.2830	60	.406	.482	278	115	130
1/0	19	.3620	80	.530	.606	441	150	170
2/0	19	.4050	80	.579	.651	538	175	195
4/0	19	.5120	80	.688	.756	808	230	260
350	37	.6610	95	.854	.930	1290	310	350
500	37	.7900	95	.983	1.059	1788	380	430
750	61	.9680	110	1.200	1.276	2638	475	535

Available in colors: gray, green, red, blue, black, red with black stripe, blue with black stripe, and gray with black stripe

CONNECT WITH US:





TelcoFlex® L4 Telecom Power Wire



SIZE	STRANDING	NOMINAL CONDUCTOR DIAMETER (INCHES)	INSUL. MIN. AVG. WALL (MILS)	NOMINAL INSUL. DIAM. (INCHES)	MAX D.C. RES @ 20°C (OHMS/MFT)	APPROX. WEIGHT (lb/1000ft)	AMPACITY PER NEC TABLE 310.15(B)(16)	
							75°C	90°C
8	41	.153	60	.277	0.679	93	50	55
6	65	.186	60	.312	0.436	136	65	75
4	126	.260	60	.383	0.274	212	85	95
2	168	.305	60	.438	0.172	280	115	130
1/0	266	.392	80	.555	0.109	450	150	170
2/0	342	.455	80	.618	0.087	562	175	195
4/0	532	.577	80	.745	0.054	828	230	260
350	888	.760	95	.953	0.033	1291	310	350
500	1221	.890	95	1.090	0.023	1776	380	430
750	1850	1.094	110	1.320	0.016	2740	475	535

Available in colors: gray, green, red, blue, black, red with black stripe, and blue with black stripe

TelcoFlex®-G L5 Telecom Grounding Cable



CONDUCTOR SIZE (AWG OR KCMIL)	STRANDING CLASS B NO. OF STRANDS	DIAMETER OVER CONDUCTOR (INCHES)	INSULATION THICKNESS (MILS)	APPX. OD (INCHES)	NOMINAL WEIGHT (LBS/MFT)	AMPACITY FOR 600V NEC TABLE 310.15 (B) (16)+	
						75°C	90°C
10	7	0.113	30	0.173	29	35	40
8	7	0.142	45	0.232	61	50	55
6	7	0.178	45	0.268	99	65	75
4	7	0.225	45	0.315	146	85	95
2	7	0.283	45	0.373	238	115	130
1	19	0.322	55	0.432	290	130	145

TelcoFlex®-G L6 Telecom Grounding Cable



CONDUCTOR SIZE (AWG OR KCMIL)	STRANDING CLASS B NO. OF STRANDS	DIAMETER OVER CONDUCTOR (INCHES)	INSULATION THICKNESS (MILS)	APPX. OD (INCHES)	NOMINAL WEIGHT (LBS/MFT)	AMPACITY FOR 600V NEC TABLE 310.15 (B) (16)+	
						75°C	90°C
10	104++	0.078	30	0.138	32	35	40
8	41	0.142	45	0.246	68	50	55
6	65	0.186	45	0.276	99	65	75
4	154	0.263	45	0.353	155	85	95
2	168	0.315	45	0.405	228	115	130
1	224	0.367	55	0.477	309	130	145

TelcoFlex[®] HYBRID FIBER POWER CABLE

WE LISTENED:


Finding reliable cable to simultaneously provide both power and data connectivity can be a challenging process. Not to mention, hybrid fiber cable is a design requirement of top tier carriers in the United States.

THE SOLUTION:

Made in the USA from the highest quality copper with a 70-year proven history in copper conductor production, Southwire's TelcoFlex[®] Hybrid Fiber Power Cable is designed to deploy components of both power and data up a tower in one assembly.

APPLICATIONS AND FEATURES:

- Ideal for applications including High Power 5G Radio, Cloud-RAN (C-RAN), and Small Cell 5G Deployments
- Standard or LIW conductor configurations available
- Featuring a copper tape shield
- Bulk cable or fully terminated assemblies



ISO-Compliant
Facilities



Low Lead
Times



Custom
Configurations



Labor-Saving



Cost-Saving



OUR MISSION

Southwire is committed to inspire the lives we touch by developing innovative systems and solutions, exercising environmental stewardship, and enhancing the well-being of our communities as *We Deliver Power... Responsibly[®]* through our core tenets.



GROWING GREEN



SCAN TO
LEARN MORE

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
All Trademarks or Registered Trademark (TM/®) are owned or licensed by Southwire Company.