


SUBMERSIBLE PUMP CABLE

Solid or stranded bare copper conductors;
individuals PVC insulation;
3 or 4 twisted conductors
600 Volts, -40°C., Maximum 60°C.



APPLICATIONS

For use with submersible pumps and irrigation equipment. For wiring only between equipment located at water wellheads and motors of submersible pumps installed in deep wells.

SPECIFICATIONS

- UL Spec. No. 493
- CSA Spec. C22.2. No. 75; LL90458

CONSTRUCTION

Solid or stranded bare copper conductors; individual PVC insulation; twisted without fillers.



Southwire
One Southwire Drive
Carrollton, Ga. 30119 USA



greenSpec
RoHS Compliant

Copyright 2010, Southwire Company.
All Rights Reserved.

®Southwire is a registered trademark
of Southwire Company.

Submersible Pump Cable

SIZE AWG	NO. OF CONDS.	COND. STRD.	MIN. GRD. WIRE AWG	INSUL. THICKNESS		NOMINAL O.D.		(AMPS)	NET WEIGHT	
				(mm)	(in.)	(mm)	(in.)		kg/km	lbs/Mft
14	3	1	14	1.52	.06	10.1	.398	15	116.05	77.99
12	3	1	12	1.52	.06	11.02	.434	20	157.14	105.61
14	3	7	14	1.52	.06	10.57	.416	15	123.34	82.89
12	3	7	8	1.52	.06	13.61	.536	20	239.36	160.86
12	3	7		1.52	.06	11.61	.457	20	167.35	112.47
10	3	7	10	1.52	.06	13.26	.522	30	232.02	155.93
14	4	1	14	1.52	.06	11.29	.444	15	154.73	103.98
12	4	1	12	1.52	.06	12.31	.485	20	209.52	140.81
10	4	1	10	1.52	.06	13.61	.536	30	293.21	197.05
14	4	7	14	1.52	.06	11.82	.465	15	164.45	110.52
12	4	7	12	1.52	.06	12.97	.511	20	223.14	149.96
12	4	7	8	1.52	.06	12.97	.511	20	295.14	198.35
10	4	7	10	1.52	.06	14.29	.562	30	309.36	207.9
8	4	7	10	2.03	.08	18.74	.738	40	460.7	309.61
6	4	7	8	2.03	.08	21.07	.83	55	675.85	454.2

* Number of Conductors includes green ground wire.



Southwire
One Southwire Drive
Carrollton, Ga. 30119 USA



greenSpec™
RoHS Compliant

Copyright 2010, Southwire Company.
All Rights Reserved.

®Southwire is a registered trademark
of Southwire Company.