Southwire® CANADA

HVTECK SPECIFICATIONS

HVTECK AL 3/C 280TRXLPE TS PVC AIA PVC 28KV 100% CSA

PRODUCT HIGHLIGHTS

Southwire's 28KV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL) and 105°C for use in harsh Canadian environments. For installation in cable trays, duct banks, direct burial, troughs, continuous rigid cable supports and concrete encaseable.

CONSTRUCTION

Conductor
- Class B - compact stranded -8000 Series Aluminum -ACM

Options
- Class B compact stranded copper
- Class B compressed stranded copper
- Strand blocking technology
- Tinning on copper conductors

Conductor Shield
- Extruded semi-conducting thermosetting polymeric layer

Insulation
- TR-XLPE - (Tree Retardent Cross Linked Polyethylene)
- Thickness: 0.28 inches (7.11mm) - nominal
- Insulation level: 100% - grounded system
- 105°C rated

Insulation Shield
- Extruded Semi-conducting thermosetting polymeric layer
- CSA 68.10 - Shield Removal/termination requirements are printed on the surface
- Phase identification as per ICEA Method 3, using printed circuit numbers
- Meets requirement of ICEA but built to CSA standards

Copper Tape Shield
- Helically wrapped 5 mil copper tape with 25% overlap

Bonding Conductor
- Class B compressed stranded bare copper - in accordance with ASTM B3 and B8

Fillers
- Non-wicking, non-hygroscopic

Inner Jacket
- Black PVC
- Thickness:
  No.1 AWG to No.3/0 AWG = 0.11 inches (2.79mm)
  No.4/0 AWG to 500 kcmil = 0.14 inches (3.56mm)

Armour
- Aluminum Interlocked Armour (AIA)
- Optional Galvanized Steel Interlocked Armour (GSIA)

Overall Jacket
- Black PVC (optional colours available)
- Nominal Thickness:
  No.1 AWG to No.3/0 AWG = 0.075 inches (1.91mm)
  No.4/0 AWG to 500 kcmil = 0.085 inches (2.16mm)

Typical Print Legend
- (CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CPT AL 280 TRXLPE AIA 28KV 100% INS LEVEL 25% TS SUN RES 105° FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

TABLE 1 - WEIGHTS & MEASUREMENTS

	Conductor Size *	Conductor Diameter		Diameter Over Insulation		Diameter Over Insulation Shield		Bonding Cond. Size	Diameter Over Inner Jacket		Diameter Over Armour		Approx. Overall Diameter		Minimum Bend Radius		Approx. Weight of Cable		Max. Reel Weight (reel and cable) **		Max. Reel Diameter / Width **		Max. Length of Cable on Reel **	
HVTECK Product Code	AWG or Kcmil	inches	mm	inches	mm	inches	mm	AWG	inches	mm	inches	mm	inches	mm	inches	mm	lb / 1000ft	kg/km	lbs	kg	inches	m	feet	m
AL280S95-001	1(19)	0.299	7.6	0.889	22.6	0.969	24.6	6	2.356	59.8	2.686	68.2	2.836	72.0	19.9	504	2985	4442	8420	3819	108/70.5	2.74/1.79	2300	701
AL280S95-010	1/0(19)	0.336	8.5	0.926	23.5	1.006	25.6	6	2.436	61.9	2.766	70.3	2.916	74.1	20.4	518	3156	4696	8498	3854	108/70.5	2.74/1.79	2200	671
AL280S95-020	2/0(19)	0.376	9.6	0.966	24.5	1.046	26.6	6	2.523	64.1	2.853	72.5	3.003	76.3	21.0	534	3352	4988	8761	3974	108/70.5	2.74/1.79	2150	655
AL280S95-030	3/0(19)	0.423	10.7	1.013	25.7	1.093	27.8	6	2.624	66.7	2.954	75.0	3.104	78.8	21.7	552	3588	5339	8910	4042	108/70.5	2.74/1.79	2050	625
AL280S95-040	4/0(19)	0.475	12.1	1.065	27.1	1.145	29.1	6	2.796	71.0	3.126	79.4	3.296	83.7	23.1	586	4109	6114	8129	3687	108/70.5	2.74/1.79	1600	488
AL280S95-250	250(37)	0.520	13.2	1.120	28.4	1.200	30.5	4	2.915	74.0	3.245	82.4	3.415	86.7	23.9	607	4448	6619	8227	3732	108/70.5	2.74/1.79	1500	457
AL280S95-350	350(37)	0.616	15.6	1.216	30.9	1.296	32.9	4	3.123	79.3	3.453	87.7	3.623	92.0	25.4	644	5031	7486	7089	3215	108/70.5	2.74/1.79	1100	335
AL280S95-500	500(37)	0.736	18.7	1.336	33.9	1.416	36.0	3	3.382	85.9	3.712	94.3	3.882	98.6	27.2	690	5863	8724	7711	3498	108/70.5	2.74/1.79	1050	320

NOTE: These are minimum average dimensions as per CSA Standards.

* Other conductor sizes and outer jacket colours are available upon request. (#s in brackets represent # of strands / conductor)

** Longer maximum lengths may be possible. Standard sizes and lengths may be supplied. Reel sizes are not guaranteed. The factory reserves the right to make changes as necessary to optimize manufacturing requirements.

© 2016 Southwire Company, LLC. All Rights Reserved.

SPS_S95_INDUSTRIAL-E(07/20/2016) Rev: 3.06R

HVTECK SPECIFICATIONS

HVTECK AL 3/C 280TRXLPE TS PVC AIA PVC 28KV 100% CSA

DESIGN

Qualification Standards

- CSA C68.10 - Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 - Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA C22.2 No. 174 - Cables in Hazardous Locations
- ICEA S-93-639 (NEMA WC 74) 5 to 46 kV - Shielded Power Cable
- AEIC CS-8 - Qualification Testing Requirements

Flame Test Ratings

- FT1 - Flame Test - (1,706 BTU/Hr. nominal - Vertical Wire Flame Test)
- FT4, Flame Test - (70,000 BTU/Hr. - Vertical Tray Flame Test)
- IEEE 1202 - Flame Test - (70,000 BTU/Hr. - Vertical Tray Test)
- IEEE 383 - Flame Test - (70,000 BTU/Hr.)
- ICEA T-29-520 - Vertical Cable Tray Flame Test - (210,000 BTU/Hr)

Product Ratings

- CSA C22.2 No. 2556 & No. 0.3. - Wire and Cable Test Methods
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA FT4 - for Flame Retardancy rating
- CSA SUN RES - for Sunlight Resistant rating

Operating Temperatures

- -40°C - CSA Cold Bend and Impact Temperature
- -25°C - Min. Installation Temperature
- 105°C - Max Continuous Operating Temperature
- 140°C for Emergency Overload Temperature
- 250°C for Short Circuit Temperature



End View

TABLE 2 - ENGINEERING SPECIFICATIONS

HVTECK Product Code	Maximum Pulling Tension		DC Resistance @ 25°C R_{DC}		AC Resistance @ 90°C 60 Hz (triplex formation) R_{AC}		Inductance L		Capacitance C		Inductive Reactance @ 60Hz (triplexed) X_L		Capacitive Reactance @ 60Hz (triplexed) X_C		Positive - Sequence Impedance*	Zero - Sequence Impedance*	Short Circuit Current (each phase conductor) @ 60Hz	Allowable Ampacities in Ventilated Cable Tray †	Allowable Ampacities Directly Buries in Earth ‡
	lb	Newtons	Ω / 1000 ft.	Ω / km	Ω / 1000 ft.	Ω / km	mH / 1000 ft	mH / km	µF / 1000 ft	µF / km	Ω / 1000 ft.	Ω / km	MΩ • 1000ft	MΩ • km	Ω / 1000ft	Ω / 1000ft	kAmps	Amps	Amps
AL280S95-001	1506	6701	0.211	0.692	0.265	0.870	0.1240	0.4069	0.0358	0.1174	0.0467	0.1534	0.0742	0.0226	0.266 + j0.049	0.633 + j0.364	3.9	158	177
AL280S95-010	1901	8455	0.168	0.551	0.211	0.693	0.1194	0.3917	0.0384	0.1262	0.0450	0.1477	0.0690	0.0210	0.212 + j0.047	0.576 + j0.349	5.0	181	200
AL280S95-020	2396	10657	0.133	0.436	0.167	0.549	0.1151	0.3776	0.0413	0.1355	0.0434	0.1424	0.0642	0.0196	0.168 + j0.046	0.529 + j0.335	6.3	208	228
AL280S95-030	3020	13435	0.105	0.345	0.132	0.433	0.1108	0.3636	0.0446	0.1464	0.0418	0.1371	0.0594	0.0181	0.132 + j0.044	0.490 + j0.319	7.9	239	258
AL280S95-040	3809	16942	0.084	0.274	0.105	0.345	0.1068	0.3504	0.0483	0.1584	0.0403	0.1321	0.0549	0.0167	0.106 + j0.042	0.458 + j0.302	9.9	273	292
AL280S95-250	4500	20017	0.071	0.232	0.089	0.292	0.1043	0.3424	0.0508	0.1667	0.0393	0.1291	0.0522	0.0159	0.089 + j0.041	0.437 + j0.286	11.8	302	321
AL280S95-350	6300	28024	0.051	0.166	0.064	0.209	0.0990	0.3249	0.0573	0.1880	0.0373	0.1225	0.0463	0.0141	0.064 + j0.039	0.402 + j0.261	16.5	368	385
AL280S95-500	9000	40034	0.035	0.116	0.045	0.147	0.0939	0.3081	0.0654	0.2145	0.0354	0.1162	0.0406	0.0124	0.045 + j0.037	0.371 + j0.234	23.5	454	462

* Calculations are based on 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on Table D17N of the 2015 Canadian Electrical Code Part I (40°C Ambient Air Temperature, indoor installation)

‡ Ampacities are based on Table D17E of the 2015 Canadian Electrical Code Part I

© 2016 Southwire Company, LLC. All Rights Reserved.

SPS_S95_INDUSTRIAL-E(07/20/2016) Rev: 3.06R