

# DURAGROUND 600V RW90 CSA FT4 TRAY RATED GROUND CABLE

Single Copper Conductors, XLPE Insulation, Sunlight Resistant, 600V 90C MAX, -40C MIN, Gasoline & Oil Resistant



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type RW90

## APPLICATIONS AND FEATURES:

Suitable for installation in Cable Trays, Underground Duct Banks and Direct Burial - As per CE Code limitations (see Rule 12-2202) for grounding and bonding applications.

## SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables Type RW90
- CSA C22.2 No.230 Tray Cables - Rated TC-ER
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA SUN RES - for Sunlight Resistant rating
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- RoHS-2 (European Directive 2011/65/EU)

## SAMPLE PRINT LEGEND:

E30117 MASTER-DESIGN {UL} XXXX KCMIL CU RHH-RHW-2 600V FOR CT USE FT4 SR PR I OR PR II 90{D}C WET OR DRY -40 {D}C --- {CSA} LL90458 XXXX KCMIL (XXX mm<sup>2</sup>) RW90 600V FT4 SR -40{D}C XLPE --- RoHS {MMM/DD/YYYY}



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Raceway 90°C†
	AWG/Kcmil	No.	inch	mil	inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
649039	2	7	0.277	45	0.367	234	1.7	531	0.162	0.203	0.032	15089	130
TBA	1/0	19	0.360	55	0.470	361	1.9	845	0.102	0.128	0.028	24011	170
649041◇	2/0	19	0.404	55	0.514	450	2.1	1065	0.081	0.102	0.027	30264	195
TBA	3/0	19	0.454	55	0.564	562	2.3	1342	0.064	0.081	0.027	38154	225
649043◇	4/0	19	0.510	55	0.620	703	2.5	1693	0.051	0.064	0.026	48114	260
TBA	250	37	0.558	65	0.688	832	2.8	2000	0.043	0.055	0.027	56845	290
649054◇	350	37	0.661	65	0.791	1151	3.2	2800	0.031	0.040	0.026	79583	350
649056◇	500	37	0.789	65	0.919	1627	3.7	4000	0.022	0.029	0.025	113690	430
649058◇	750	61	0.968	80	1.128	2435	5.6	6000	0.014	0.020	0.025	170535	535
649060◇	1000	61	1.117	80	1.277	3223	6.4	8000	0.011	0.017	0.025	227380	615

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Phase Short Circuit Current @ 60Hz	Allowable Ampacity In Raceway 90°C†
	AWG/Kcmil	No.	mm	mm	mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp	Amp
649039	2	7	7.04	1.14	9.32	348	43.18	2363	0.5315	0.67	0.1050	15089	130
TBA	1/0	19	9.14	1.40	11.94	537	48.26	3760	0.3346	0.42	0.0919	24011	170
649041◇	2/0	19	10.26	1.40	13.06	670	53.34	4739	0.2657	0.33	0.0886	30264	195
TBA	3/0	19	11.53	1.40	14.33	836	58.42	5972	0.2100	0.27	0.0886	38154	225
649043◇	4/0	19	12.95	1.40	15.75	1046	63.50	7534	0.1673	0.21	0.0853	48114	260
TBA	250	37	14.17	1.65	17.48	1238	71.12	8900	0.1411	0.18	0.0886	56845	290
649054◇	350	37	16.79	1.65	20.09	1713	81.28	12460	0.1017	0.13	0.0853	79583	350
649056◇	500	37	20.04	1.65	23.34	2421	93.98	17800	0.0722	0.10	0.0820	113690	430
649058◇	750	61	24.59	2.03	28.65	3624	142.24	26700	0.0459	0.07	0.0820	170535	535
649060◇	1000	61	28.37	2.03	32.44	4796	162.56	35600	0.0361	0.06	0.0820	227380	615

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.

