

Southwire[™] LIQUIDTIGHT CATALOG



SOUTHWIRE.COM

LOUDTIGHT FITINGS

Ensure safe electrical service by making a secure connection with Southwire Liquidtight Connectors. By sealing out water, oil, dirt, dust and fumes, our Liquidtight Connectors and Conduit provide protection for electrical service in areas exposed to contaminants and vibrations and widely used in the mechanical, H/VAC and automotive industries.


Zinc Liquidtight Connectors, Straight and 90° Malleable Iron Liquidtight Connectors, Straight, 90 and 45° Malleable Iron Liquidtight Connectors, Straight, 90 and 45° with Lug Metallic Liquidtight Conduit NM Liquidtight Connectors, Straight and 90° NM Liquidtight Conduit Combination Couplings



STRAIGHT LIQUIDTIGHT CONNECTORS ZINC



470





FEATURES


- Liquidtight, raintight, oiltight
- Straight connectors
- Assembled with a die cast locknut
- APPLICATIONS
 - For use with metallic and non-metallic "Type B" liquidtight conduit
- STANDARD MATERIAL
 - Zinc die cast
- CERTIFICATIONS
 - cULus

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
470	3/8" 1/2" KO	20	200	36	1.446"	1.26"	.40"
471	1/2"	20	200	40	1.50"	1.385"	.42"
472	3/4"	10	100	23	1.603"	1.72"	.42"
473	1"	5	50	20	1.792"	1.90"	.55"
474	1-1/4"	5	50	30	1.90"	2.29"	.546"
475	1-1/2"	2	20	15	1.737"	2.633"	.52"
476	2"	2	20	24	2.08"	3.156"	.585"
477	2-1/2"		1	1	3.025"	4.205"	.775"
478	3"		1	2	3.53"	4.91"	.92"
479	3-1/2"		1	3	3.66"	5.47"	.92"
480	4"		1	4	3.875"	5.925"	.987"

WITH INSULATED THROAT - ZINC



470i



5

FEATURES


- Liquidtight, raintight, oiltight
- Straight connectors
- Assembled with a die cast locknut
- Insulated throat protects against
- abrasion damage
 - For use with metallic and non-metallic
 - "Type B" liquidtight conduit
- STANDARD MATERIAL
 - Zinc die cast

• cULus

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	А	В	C
4701	3/8" 1/2" KO	20	200	40	1.446"	1.260"	.40"
4711	1/2"	20	200	34	1.50"	1.385"	.42"
4721	3/4"	10	100	25	1.603"	1.72"	.42"
4731	1"	5	50	22	1.792"	1.90"	.550"
4741	1-1/4"	5	50	34	1.90"	2.29"	.546"
4751	1-1/2"	2	20	18	1.937"	2.633"	.52"
4761	2"	2	20	28	2.08"	3.156"	.585"
LQA-1250-I	2-1/2"		1	1	3.025"	4.205"	.775"
LQA-1300-I	3"		1	2	3.53"	4.91"	.92"
LQA-1350-I	3-1/2"		1	3	3.66"	5.47"	.92"
LQA-1400-I	4"		1	4	3.875"	5.925"	.987"

STRAIGHT LIQUIDTIGHT CONNECTORS WITH INSULATED THROAT - MALLEABLE IRON





470S

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	А	В
470S	3/8" 1/2" KO	20	200	31	1.18"	1.72"
471S	1/2"	20	200	33	1.36"	1.73"
472S	3/4"	10	100	25	1.61"	1.81"
473S	1"	5	50	18	1.89"	1.85"
474S	1-1/4"	5	50	28	2.39"	2.05"
475S	1-1/2"	2	20	15	2.62"	2.38"
476S	2"	2	20	22	3.24"	2.49"
477S	2-1/2"		1	2	3.89"	3.21"
478S	3"		1	3	4.74"	3.37"
479S	3-1/2"		1	4	5.31"	3.40"
480S	4"		1	5	5.82"	3.66"
480SA*	5"		1	10	6.06"	4.63"
480SB*	6"		1	13	7.75"	4.94"

*480SA and 480SB not UL listed

FEATURES

- Liquidtight, raintight, oiltight
- Tapered threaded male hub NPT
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius
- Zinc electro plated for excellent durability

APPLICATIONS

- To secure, ground and seal liquidtight conduit to a box or enclosure
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I


STANDARD MATERIAL

- Malleable iron
- Steel locknut
- **STANDARD FINISH**
- Zinc plated
 CERTIFICATIONS
 - UL Standard: UL 514B
 - Fed. Spec: W-F-406E, W-F-406D
 - •NEMA: FB 1-2014

STRAIGHT LIQUIDTIGHT CONNECTORS WITH INSULATED THROAT - STEEL



470ST





FEATURES

- Liquidtight, raintight, oiltight
- Industrial specification grade, screw machined steel
- Corrosion resistant protection from moisture & oils

APPLICATIONS

- Bonds liquidtight conduit to box or enclosure
- Straight type
- **STANDARD MATERIAL**

Steel
 STANDARD FINISH

• Zinc plated

CERTIFICATIONS

cULus

UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div. 2, Class II Div. 1 and 2, Class III Div. 1 and 2 are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-1

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
470ST	3/8" 1/2" KO	20	200	25	1.09"	1.19"	.63"
471ST	1/2"	20	200	31	1.19"	1.34"	.63"
472ST	3/4"	10	100	23	1.43"	1.43"	.63"
473ST	1"	5	50	18	1.75"	1.63"	.66"
474ST	1-1/4"	5	50	23	2.16"	1.84"	.67"
475ST	1-1/2"	2	20	12	2.38"	2"	.72"
476ST	2"	2	20	15	2.88"	2.13"	.72"

WITH INSULATED THROAT - 304 STAINLESS STEEL



LTCSS-38



PART #	SIZE	MASTER QTY.
LTCSS-38	3/8"	20
LTCSS-50	1/2"	20
LTCSS-75	3/4'	10
LTCSS-100	1"	5
LTCSS-125	1-1/4"	5
LTCSS-150	1-1/2"	5
LTCSS-200	2"	5

FEATURES

- For use with metallic and non-metallic type B
- Connectors can be easily disassembled and reused
- Sealing washers included

Heavy duty stainless steel lock nuts included
 APPLICATIONS

- Connects liquid-tight conduit to a box or enclosure in wet, damp & corrosive local
- enclosure in wet, damp & corrosive locations **STANDARD MATERIAL**
 - 304 stainless steel

CERTIFICATIONS


UL Listed, CSA Listed

STRAIGHT LIQUIDTIGHT CONNECTORS

WITH INSULATED THROAT - MALLEABLE IRON HOT DIP GALVANIZED



471HDG



FEATURES

- Hot dip galvanized
- Liquidtight, raintight, oiltight
- Tapered threaded male hub NPT
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius

APPLICATIONS

- To secure, ground and seal liquidtight conduit to a box or enclosure
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes

3/8" through 1-1/2" under NEC 351-I

- STANDARD MATERIAL
 - Malleable iron
 - Steel locknut
- Hot dip galvanized
- Hot dip gaiva
 CERTIFICATIONS
- - UL Standard: UL 514B
 Fed. Spec: W-F-406E, W-F-406D
 - NEMA, ED 1 2014
 - •NEMA: FB 1-2014



PART #	CONDUIT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В
471HDG	1/2"	20	200	33	1.36"	1.73"
472HDG	3/4"	10	100	24	1.61"	1.81"
473HDG	1"	5	50	18	1.89"	1.85"
474HDG	1-1/4"	5	50	30	2.39"	2.05"
475HDG	1-1/2"	2	20	15	2.62"	2.38"
476HDG	2"	2	20	23	3.24"	2.49"
477HDG	2-1/2"		1	2	3.89"	3.21"
478HDG	3"		1	3	4.74"	3.37"
479HDG	3-1/2"		1	5	5.31"	3.40"
480HDG	4"		1	5	5.82"	3.66"

UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div. 2, Class II Div. 1 and 2, Class III Div. 1 and 2 are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-1

STRAIGHT LIQUIDTIGHT CONNECTORS WITH GROUNDING LUG - MALLEABLE IRON



471SGR





В

US

PART #	SIZE	LUG SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В
ALUMINUM	GROUNDIN	G LUG					
470SGR	3/8"	14-4	10	100	22	1.18"	1.72"
471SGR	1/2"	14-4	10	100	23	1.36"	1.73"
472SGR	3/4"	14-4	5	50	18	1.61"	1.81"
473SGR	1"	14-4	5	50	24	1.89"	1.85"
474SGR	1-1/4"	14-4	2	20	16	2.39"	2.05"
475SGR	1-1/2"	14-4	2	20	18	2.62"	2.38"
476SGR	2"	14-4	2	20	27	3.24"	2.49"
477SGR	2-1/2"	1/0-14		1	7	3.89"	3.21"
478SGR	3"	1/0-14		1	8	4.74"	3.37"
479SGR	3-1/2"	6/250		1	8	5.31"	3.40"
480SGR	4"	6/250		1	10	5.82"	3.66"
COPPER GRO	DUNDING L	JG					
471CSGR	1/2"	14-4	10	100	24	1.36"	1.73"
472CSGR	3/4"	14-4	5	50	16	1.61"	1.81"
473CSGR	1"	14-4	5	50	22	1.89"	1.85"
474CSGR	1-1/4"	14-4	2	20	14	2.39"	2.05"
475CSGR	1-1/2"	14-4	2	20	17	2.62"	2.38"
476CSGR	2"	14-4	2	20	26	3.24"	2.49"
MSTR-250-CL	2-1/2"	1/0-14		1	7	3.89"	3.21"
MSTR-300-CL	3"	1/0-14		1	8	4.74"	3.37"
MSTR-350-CL	3-1/2"	6/250		1	8	5.31"	3.40"
MSTR-400-CL	4"	6/250		1	10	5.82"	3.66"

FEATURES

- Liquidtight, raintight, oiltight
- Aluminum or Copper Lay-in grounding lug
 Insulated throat protects conductors from abrasion damage
- Zinc electro plated for excellent durability

APPLICATIONS

- Use to connect liquidtight conduit and terminate an external bonding conductor that runs parallel to the conduit
- The NEC code specifies length limitations and that the bonding jumper must be parallel to the conduit
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL

- Malleable iron
- Steel locknut
- Aluminum or Copper lug

STANDARD FINISH

Zinc plated


CERTIFICATIONS

- •UL 467 UL 486A
- Fed. Spec: W-S-610E
- •NEMA: GR 1-2017

90° LIQUIDTIGHT CONNECTORS ZINC



491



FEATURES

- Liquidtight, raintight, oiltight
- 90° connectors
- Assembled with a die cast locknut

APPLICATIONS

- For use with metallic and non-metallic "Type B" liquidtight conduit
- STANDARD MATERIAL
 - Zinc die cast
- CERTIFICATIONS

cULus

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
490	3/8" 1/2" KO	10	100	27	2.062"	2.34"	.52"
491	1/2"	10	100	28	2.22"	2.34"	.52"
492	3/4"	10	100	38	2.55"	3.55"	.68"
493	1"	5	50	32	2.82"	3.785"	.67"
494	1-1/4"	2	20	20	3.362"	3.96"	.70"
495	1-1/2"	2	20	26	3.45"	4.13"	.70"
496	2"	1	10	19	4.036"	4.70"	.57"
497	2-1/2"		1	4	5.215"	5.375"	.77"
498	3"		1	5	6.10"	6.50"	1.10"
499	3-1/2"		1	6	6.715"	7.45"	1.10"
500	4"		1	7	6.78"	8"	1.10"

US

WITH INSULATED THROAT - ZINC



490i



FEATURES

- Liquidtight, raintight, oiltight
- 90° connectors
- Assembled with a die cast locknut
- Insulated throat protects against abrasion damage

APPLICATIONS

• For use with metallic and non-metallic "Type B" liquidtight conduit

STANDARD MATERIAL

Zinc die cast

CERTIFICATIONS

• cULus


PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	А	В	C
4901	3/8" 1/2" KO	10	100	30	2.062"	2.34"	.52"
4911	1/2"	10	100	27	2.22"	2.34"	.52"
4921	3/4"	10	100	39	2.55"	3.55"	.68"
4931	1"	5	50	33	2.82"	3.785"	.67"
4941	1-1/4"	2	20	21	3.362"	3.96"	.70"
4951	1-1/2"	2	20	26	3.45"	4.13"	.70"
4961	2"	1	10	20	4.036"	4.70"	.57"
LQA-9250-I	2-1/2"		1	4	5.215"	5.375"	.77"
LQA-9300-I	3"		1	5	6.10"	6.50"	1.10"
LQA-9350-I	3-1/2"		1	6	6.715"	7.45"	1.10"
LQA-9400-I	4"		1	7	6.78"	8"	1.10"

US

90° LIQUIDTIGHT CONNECTORS WITH INSULATED THROAT - MALLEABLE IRON



⁴⁹⁰S



FEATURES

- Liquidtight, raintight, oiltight
- Suitable for wet location use
- Tapered threaded male hub NPT
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius
- Zinc electro plated for excellent durability APPLICATIONS
 - To secure, ground and seal liquidtight
 - Output to a box or enclosureUL listed liquidtight flexible metal
 - conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I
- STANDARD MATERIAL
 - Malleable iron
 - Steel locknut
- Zinc plated




PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
490S	3/8" 1/2" KO	10	100	26	1.18"	1.96"	2.47"
491S	1/2"	10	100	28	1.36"	2.10"	2.54"
492S	3/4"	10	100	41	1.61"	2.45"	2.82"
493S	1"	5	50	31	1.89"	2.83"	3.08"
494S	1-1/4"	2	20	20	2.39"	3.15"	3.53"
495S	1-1/2"	2	20	25	2.62"	3.50"	4.17"
496S	2"	1	10	19	3.24"	4.02"	4.69"
497S	2-1/2"		1	5	3.89"	6.23"	6.74"
498S	3"		1	7	4.74"	6.91"	7.52"
499S	3-1/2"		1	9	5.31"	7.57"	7.93"
500S	4"		1	14	5.82"	8.07"	8.72"

90° LIQUIDTIGHT CONNECTORS WITH INSULATED THROAT - MALLEABLE IRON HOT DIP GALVANIZED



491HDG



FEATURES

- Hot dip galvanized
- Liquidtight, raintight, oiltight
- Suitable for wet location use
- Tapered threaded male hub NPT
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius

APPLICATIONS

- To secure, ground and seal liquidtight conduit to a box or enclosure
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL

- Malleable iron
- Steel locknut
- **STANDARD FINISH**
 - Hot dip galvanized



UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div. 2, Class II Div. 1 and 2, Class III Div. 1 and 2 are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-1

PART #	CONDUIT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
491HDG	1/2"	10	100	28	1.36"	2.10"	2.54"
492HDG	3/4"	10	100	41	1.61"	2.45"	2.82"
493HDG	1"	5	50	31	1.89"	2.83"	3.08"
494HDG	1-1/4"	2	20	21	2.39"	3.15"	3.53"
495HDG	1-1/2"	2	20	25	2.62"	3.50"	4.17"
496HDG	2"		10	18	3.24"	4.02"	4.69"
498HDG	3"		1	7	4.74"	6.91"	7.52"

90° LIQUIDTIGHT CONNECTORS WITH GROUNDING LUG - MALLEABLE IRON



490SGR



490CSGR



PART #	SIZE	LUG SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
ALUMINU	M GROUN	DING LUG						
490SGR	3/8"	14-4	5	50	17	1.18"	1.96"	2.47"
491SGR	1/2"	14-4	5	50	24	1.36"	2.10"	2.54"
492SGR	3/4"	14-4	2	20	16	1.61"	2.45"	2.82"
493SGR	1"	14-4	2	20	17	1.89"	2.83"	3.08"
494SGR	1-1/4"	14-4	2	20	25	2.39"	3.15"	3.53"
495SGR	1-1/2"	14-4	2	20	29	2.62"	3.50"	4.17"
496SGR	2"	14-4	2	20	42	3.24"	4.02"	4.69"
497SGR	2-1/2"	1/0-14		1	9	3.89"	6.23"	6.74"
498SGR	3"	1/0-14		1	11	4.74"	6.91"	7.52"
499SGR	3-1/2"	6/250		1	13	5.31"	7.57"	7.93"
500SGR	4"	6/250		1	15	5.82"	8.07"	8.72"
COPPER G	ROUNDIN	IG LUG						
491CSGR	1/2"	14-4	5	50	18	1.36"	2.10"	2.54"
492CSGR	3/4"	14-4	2	20	11	1.61"	2.45"	2.82"
493CSGR	1"	14-4	2	20	15	1.89"	2.83"	3.08"
494CSGR	1-1/4"	14-4	2	20	21	2.39"	3.15"	3.53"
495CSGR	1-1/2"	14-4	2	20	26	2.62"	3.50"	4.17"
496CSGR	2"	14-4	2	20	41	3.24"	4.02"	4.69"

FEATURES

- Liquidtight, raintight, oiltight
- Aluminum or Copper Lay-in grounding lug • Insulated throat protects conductors from
- abrasion damage
- Zinc electro plated for excellent durability

APPLICATIONS

- Use to connect liquidtight conduit and terminate an external bonding conductor that runs parallel to the conduit
- The NEC code specifies length limitations and that the bonding jumper must be parallel to the conduit
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL

- Malleable iron
- Steel locknut
- Aluminum or Copper lug

STANDARD FINISH

- Zinc plated
- CERTIFICATIONS
 - •UL 467 UL 486A
 - Fed. Spec: W-S-610E
 - •NEMA: GR 1-2017

90° LIQUIDTIGHT CONNECTORS 304 STAINLESS STEEL



LTCSS-5090

PART #

LTCSS-5090



MASTER QTY.

20

E,	Δт	111	RF	S	
-		0		0	

F

- For use with metallic and non-metallic type B
 Connectors can be easily disassembled and
- Connectors can be easily disassembled and reused
- Sealing washers included
- Heavy duty stainless steel lock nuts included
 APPLICATIONS
 - Connects liquid-tight conduit to a box or enclosure in wet, damp & corrosive locations

STANDARD MATERIAL

- 304 stainless steel CERTIFICATIONS
 - UL Listed, CSA Listed

LTCSS-7590	3/4'	20
LTCSS-10090	1"	5
LTCSS-12590	1-1/4"	5
LTCSS-15090	1-1/2"	5
LTCSS-20090	2"	5


SIZE

1/2"

45° LIQUIDTIGHT CONNECTORS WITH INSULATED THROAT - MALLEABLE IRON



²³⁰S



PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
230S	3/8" 1/2" KO	10	100	24	1.18"	1.39"	2.51"
231S	1/2"	10	100	28	1.36"	1.50"	2.51"
232S	3/4"	10	100	42	1.61"	1.73"	2.70"
233S	1"	5	50	32	1.89"	2.11"	3.05"
234S	1-1/4"	2	20	22	2.39"	2.56"	3.65"
235S	1-1/2"	2	20	32	2.62"	2.77"	4.01"
236S	2"	2	20	49	3.24"	3.38"	4.64"
237S	2-1/2"		1	5	3.89"	4.68"	6.46"
238S	3"		1	7	4.74"	5.33"	7.01"
239S	3-1/2"		1	10	5.31"	5.81"	7.33"
240S	4"		1	12	5.82"	6.42"	8.20"

FEATURES

- Liquidtight, raintight, oiltight
- Suitable for wet locations
- Tapered threaded male hub NPT
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius
- Zinc electro plated for excellent durability

APPLICATIONS

- To secure, ground and seal liquidtight conduit to a box or enclosure
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL


- Malleable iron
- Steel locknut
 STANDARD FINISH
 - Zinc plated
- CERTIFICATIONS • cULus

45° LIQUIDTIGHT CONNECTORS

WITH INSULATED THROAT - MALLEABLE IRON HOT DIP GALVANIZED



231HDG



FEATURES

- Hot dip galvanized
- · Liquidtight, raintight, oiltight
- Suitable for wet locations
- Tapered threaded male hub NPT
 Insulated threat protects conduct
- Insulated throat protects conductors from abrasion damage
- Compact slim diameter with small turning radius

APPLICATIONS

- To secure, ground and seal liquidtight conduit to a box or enclosure
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL

- Malleable iron
- Steel locknut
- **STANDARD FINISH**

Hot dip galvanized

CERTIFICATIONS

cULus

S

UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div. 2, Class II Div. 1 and 2, Class III Div. 1 and 2 are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-1

PART #	CONDUIT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
231HDG	1/2"	10	100	25	1.36"	1.50"	2.51"
232HDG	3/4"	10	100	35	1.61"	1.73"	2.70"
233HDG	1"	5	50	26	1.89"	2.11"	3.05"
234HDG	1-1/4"	2	20	19	2.39"	2.56"	3.65"
235HDG	1-1/2"	2	20	23	2.62"	2.77"	4.01"
236HDG	2"	2	20	34	3.24"	3.38"	4.64"

45° LIQUIDTIGHT CONNECTORS WITH GROUNDING LUG - MALLEABLE IRON

B



230SGR



230CSGR



- Liquidtight, raintight, oiltight
- Aluminum or Copper Lay-in grounding lug
 Insulated throat protects conductors
- from abrasion damage
- Zinc electro plated for excellent durability

APPLICATIONS

- Use to connect liquidtight conduit and terminate an external bonding conductor that runs parallel to the conduit
- The NEC code specifies length limitations and that the bonding jumper must be parallel to the conduit
- UL listed liquidtight flexible metal conduit fittings are suitable for use in the following hazardous locations under: NEC 501-4(b), 502-4(a), (2)503-3(a) Class 1 Div.2, Class II Div.1 and 2, Class III Div.1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-I

STANDARD MATERIAL

- Malleable iron
- Steel locknut
- Aluminum or Copper lug

STANDARD FINISH

• Zinc plated CERTIFICATIONS


- •UL 467 UL 486A
- Fed. Spec: W-S-610E
- •NEMA: GR 1-2017

PART #	SIZE	LUG SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C			
ALUMINU	ALUMINUM GROUNDING LUG										
230SGR	3/8"	14-4	5	50	16	1.18"	1.39"	2.51"			
231SGR	1/2"	14-4	5	50	17	1.36"	1.50"	2.51"			
232SGR	3/4"	14-4	2	50	24	1.61"	1.73"	2.70"			
233SGR	1"	14-4	2	20	16	1.89"	2.11"	3.05"			
234SGR	1-1/4"	14-4	2	20	24	2.39"	2.56"	3.65"			
235SGR	1-1/2"	14-4	2	20	26	2.62"	2.77"	4.01"			
236SGR	2"	14-4	2	20	37	3.24"	3.38"	4.64"			
237SGR	2-1/2"	1/0-14		1	8	3.89"	4.68"	6.46"			
238SGR	3"	1/0-14		1	11	4.74"	5.33"	7.01"			
239SGR	3-1/2"	6/250		1	12	5.31"	5.81"	7.33"			
240SGR	4"	6/250		1	14	5.82"	6.42"	8.20"			
COPPER G	ROUNDING	LUG									
231CSGR	1/2"	14-4	5	50	17	1.36"	1.50"	2.51"			
232CSGR	3/4"	14-4	5	50	24	1.61"	1.73"	2.70"			
233CSGR	1"	14-4	2	20	16	1.89"	2.11"	3.05"			
234CSGR	1-1/4"	14-4	2	20	24	2.39"	2.56"	3.65"			
235CSGR	1-1/2"	14-4	2	20	26	2.62"	2.77"	4.01"			
236CSGR	2"	14-4	2	20	37	3.24"	3.38"	4.64"			

RIGID TO FLEXIBLE METAL CONDUIT COMBINATION COUPLING

SQUEEZE CONNECTOR - ZINC





FEATURES

- · Female hub threads NPT
- RoHS compliant

APPLICATIONS

- To connect flexible metal conduit to rigid or IMC conduit
- STANDARD MATERIAL
- Malleable iron

STANDARD FINISH

Zinc plated

• cULus


RTF50

PART #	RIGID SIZE	FLEX SIZE	MASTER QTY.	A	В	C
RTF50	1/2"	1/2"	25	1-3/16"	1-1/2"	1-11/16"
RTF75	3/4"	3/4"	25	1-3/8"	1-3/4"	1-7/8"
RTF100	1"	1"	10	1-5/8"	1-13/16"	2-5/16"
RTF125	1 1/4"	1 1/4"	10	2"	2-5/16"	2-5/8"

(¶L)

COMBINATION COUPLINGS LIQUIDTIGHT TO RIGID - STEEL





FEATURES

- Liquidtight, raintight, oiltight
- NPSM thread
- Labor saving

APPLICATIONS

- Use to join liquidtight metal conduit (LFMC) to Rigid/IMC conduit between 2 different raceways
- Suitable for use in wet locations
- Raintight, concrete tight

STANDARD MATERIAL

Steel

STANDARD FINISH


- Zinc plated
- **CERTIFICATIONS**
 - •UL Standard: UL 514B
 - Fed. Spec: A-A-50553
 - NEMA: FB 1

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В
50SLT	3/8" - 1/2"	20	200	33	1.10"	1.78"
51SLT	1/2"	20	200	29	1.17"	1.78"
52SLT	3/4"	10	100	23	1.43"	1.94"
53SLT	1"	5	50	18	1.76"	2.19"
54SLT	1-1/4"	5	50	30	2.16"	2.23"
55SLT	1-1/2"	-	12	8	2.38"	2.62"
56SLT	2"	-	5	5	2.87"	2.67"

COMPRESSION TYPE - EMT TO LIQUIDTIGHT - STEEL



271



FEATURES

- · Liquidtight, raintight, oiltight
- Compression type
- EMT to liquidtight

Reusable ferrule

APPLICATIONS

- •Use to connect LT conduit to EMT 1/2" thru 1", ideal for rooftop HVAC air conditioners and motor hook-ups
- Can be used with EMT indoors only **STANDARD MATERIAL**

Steel

STANDARD FINISH • Zinc plated **CERTIFICATIONS**


cULus

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	А	В	C
271	1/2"	25	250	20	1.64"	1.39"	1.09"
272	3/4"	20	200	14	1.75"	1.72"	1.30"
273	1"	10	100	16	2"	1.75"	1.50"

STRAIGHT LIQUIDTIGHT CONNECTORS GRAY - NYLON










PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В
P470	3/8" 1/2" KO	25	100	7	2.04"	1.43"
P471	1/2"	25	100	6	2.11"	1.43"
P472	3/4"	10	100	8	2.20"	1.68"
P473	1"	5	50	12	2.28"	1.99"
P474	1-1/4"	5	50	12	2.46"	2.39"
P475	1-1/2"	5	20	14	2.72"	2.65"
P476	2"	2	20	9	3.05"	3.22"

BLACK - NYLON



P470B





PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В
P470B	3/8" 1/2" KO	25	100	7	2.04"	1.43"
P471B	1/2"	25	100	6	2.11"	1.43"
P472B	3/4"	10	100	8	2.20"	1.68"
P473B	1"	5	50	12	2.28"	1.99"
P474B	1-1/4"	5	50	12	2.46"	2.39"
P475B	1-1/2"	5	50	14	2.72"	2.65"
P476B	2"	2	20	9	3.05"	3.22"

FEATURES

- Liquidtight, raintight, oiltight
- For flexible non-metallic
- liquidtight tubing
- Easy assembly avoids having to remove the compression nut
- Straight type
- Gray

APPLICATIONS

• For use in wet and dry locations **STANDARD MATERIAL**

●6/6 Nylon

CERTIFICATIONS

• cULus

FEATURES

- Liquidtight, raintight, oiltight
- For flexible non-metallic
- liquidtight tubing
- Easy assembly avoids having to remove the compression nut
- Straight type
- Black

APPLICATIONS

• For use in wet and dry locations **STANDARD MATERIAL**


• 6/6 Nylon

CERTIFICATIONS

cULus

90° LIQUIDTIGHT CONNECTORS GRAY - NYLON







FEATURES

• Liquidtight, raintight, oiltight

- For flexible non-metallic liquidtight tubing
- Easy assembly avoids having to remove the compression nut
- 90° angle
- Gray

APPLICATIONS

For use in wet and dry locations

- STANDARD MATERIAL
- 6/6 Nylon


CERTIFICATIONS

• cULus

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	А	В	C
P490	3/8" 1/2" KO	10	100	9	2.56"	2.14"	1.09"
P491	1/2"	10	100	8	2.56"	2.14"	1.09"
P492	3/4"	10	100	11	2.84"	2.38"	1.30"
P493	1"	5	50	8	2.25"	2.81"	1.50"
P494	1-1/4"	2	20	8	3.96"	3.36"	2.40"
P495	1-1/2"	2	20	10	4.13"	3.45"	2.68"
P496	2"	1	10	9	4.68"	4.04"	3.31"

BLACK - NYLON





c UL us

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
P490B	3/8" 1/2" KO	10	100	9	2.56"	2.14"	1.09"
P491B	1/2"	10	100	8	2.56"	2.14"	1.09"
P492B	3/4"	10	100	11	2.84"	2.38"	1.30"
P493B	1"	5	50	8	2.25"	2.81"	1.50"
P494B	1-1/4"	2	20	8	3.96"	3.36"	2.40"
P495B	1-1/2"	2	20	10	4.13"	3.45"	2.68"
P496B	2"	1	10	9	4.68"	4.04"	3.31"

FEATURES

Liquidtight, raintight, oiltight

- For flexible non-metallic liquidtight
- tubing • Easy assembly avoids having to remove
- the compression nut • 90° angle
- Black

APPLICATIONS

For use in wet and dry locations

- STANDARD MATERIAL
 - 6/6 Nylon

CERTIFICATIONS

● cULus

AC WHIPS - NON METALLIC



ACW10

FEATURES

- Liquidtight
- •240 Volt
- Single phase A/C seal proof power whip
- Assembled with all UL components
- Available in 1/2" and 3/4" conduit size
- •4' and 6' lengths, designed for easy installation
- Resists corrosion, oil, water, outdoor, and sunlight damage

APPLICATIONS

 Connection between outside air conditioning unit and electrical power source; typically used to connect compressor to AC disconnect box

STANDARD MATERIAL

- Non-Metallic
- CERTIFICATIONS

•UL


PART #	CONDUIT Size	WIRE TYPE	WIRES	LENGTH IN FEET	WIRE SIZE	REDUCING WASHER	MASTER QTY.	WEIGHT/ CASE (LBS.)
ACW10	1/2"	#10 GAUGE STRANDED THNN	1- Black 1- Red 1- Green	4	#10	1/2" X 3/4"	12	18
ACW11	1/2"	#10 GAUGE STRANDED THNN	1- BLACK 1- RED 1- GREEN	6	#10	1/2" X 3/4"	12	23
ACW12	3/4"	#8 Gauge Stranded Thnn	1- BLACK 1- RED 1- GREEN	4	#8	3/4" X 1"	12	23
ACW13	3/4"	"#8 gauge Stranded Thnn"	1- BLACK 1- RED 1- GREEN	6	#8	3/4" X 1"	12	31
ACW1412	1/2"	#12 SOLID	2- Black 1-green	4	#12	1/2" X 3/4"	24	28
ACW1612	1/2"	#12 SOLID	2- Black 1- green	6	#12	1/2" X 3/4"	24	38
ACW16124W	1/2"	#12 SOLID 4 WIRE	1- BLACK 1- RED 1- GREEN 1- WHITE	6	#12	1/2" X 3/4"	24	20

All AC Whips include conduit, 1-NM straight and 1-NM 90° fitting and reducing washer. All wire leads are 1 foot lead wire length at each end.

STRAIGHT LIQUIDTIGHT CONNECTORS ONE PIECE TYPE - PVC



1501



FEATURES

Liquidtight, raintight, oiltight

• One piece type easily affixes to conduit

Straight

APPLICATIONS

• For use in wet and dry locations **STANDARD MATERIAL**

•PVC

CERTIFICATIONS ●UL


PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
1501	1/2"	25	100	5	1.75"	.50"	1.25"
1502	3/4"	25	100	8	1.80"	.625"	1.50"

ŰŲĽ

90° LIQUIDTIGHT CONNECTORS ONE PIECE TYPE - PVC



1522



FEATURES

Liquidtight, raintight, oiltight

• Recommended design for appliance or fixture installations

90° angle

APPLICATIONS

Dry location use

- STANDARD MATERIAL
- PVC CERTIFICATIONS

•UL

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	В	C
1521	1/2"	10	100	8	1.875"	.50"	3.125"
1522	3/4"	10	100	11	2.375"	.625"	3.50"

TOP-FLEX 1 TUBING NON-METALLIC - GRAY





FEATURES

- Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments
- UL Type B flexible nonmetallic liquidtight conduit

APPLICATIONS

- Indoor or outdoor use
- Hazardous Locations where necessary for flexible connections within hazardous locations per the following: Class 1, Div. 2 - 2005 NEC 501.10(B)(2) Class 2, Div. 1 - 2005 NEC 502.10(A)(2)
- Class 2, Div. 2 2005 NEC 502.10(B)(2)
- Class 3, Div. 1 2005 NEC 503.10(A)(2)
- Class 3, Div. 2 2005 NEC 503.10(B)

STANDARD MATERIAL

 Integral Rigid and flexible PVC construction

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ Case (LBS.)	OUTSIDE I Min.	DIAMETER MAX.	INSIDE D MIN.	iameter Max.	WALL THICKNESS
HF138	3/8"		100'	10	.69"	.71"	.484"	.504"	.21"
HF112	1/2"		100'	13	.82"	.84"	.622"	.642"	.21"
HF112R	1/2"	REEL	1000'	130	.82"	.84"	.622"	.642"	.21"
HF134	3/4"		100'	18	1.03"	1.05"	.82"	.84"	.21"
HF134R	3/4"	REEL	800'	144	1.03"	1.05"	.82"	.84"	.21"
HF11	1"		100'	25	1.29"	1.315"	1.041"	1.066"	.25"
HF11R	1"	REEL	500'	160	1.29"	1.315"	1.041"	1.066"	.25"
HF1114	1-1/4"		100'	33	1.63"	1.66"	1.38"	1.41"	.25"
HF1112	1-1/2"		50'	23	1.865"	1.90"	1.575"	1.60"	.30"
HF12	2"		50'	30	2.34"	2.375"	2.02"	2.045"	.33"

UL TYPE B FLEXIBLE NONMETALLIC LIQUIDTIGHT CONDUIT

- 3/8" through 2" trade sizes
- Use with top-flex nylon connectors straight or right angle
- May also be used with Topaz Die Cast Connectors for liquidtight conduit
- Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments
- · Resists abuse, pull, and crushing
- Smoothinside for easier wire pulling, no hazardous sharp edges or burrs; will not damage conductors
- For direct burial/poured concrete
- · Lightweight and lower installed cost

- Quick installation, cuts with utility knife or PVC cutter (CATALOG #VF28)
- Integral Rigid and flexible PVC construction
- Suitable for indoor/outdoor use: HVAC equipment machine tools motors and controls marine equipment printing equipment
 - pumps refrigeration equipment
- UV rated
- 80° C

TOP-FLEX II TUBING NON-METALLIC - BLACK



HF214

FEATURES

 Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments

APPLICATIONS

Indoor or outdoor use

- STANDARD MATERIAL
 - Integral Rigid and flexible PVC construction

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)	OUTSIDE I Min.	DIAMETER MAX.	INSIDE D Min.	iameter Max.	WALL THICKNESS
HF214	1/4"	100'	4	.56"	.575"	.385"	.405"	.17"
HF238	3/8"	100'	6	.69"	.71"	.484"	.504"	.21"
HF212	1/2"	100'	8	.82"	.84"	.622"	.642"	.21"
HF234	3/4"	100'	10	1.03"	1.05"	.82"	.84"	.21"
HF21	1"	100'	15	1.29"	1.315"	1.041"	1.066"	.25"
HF2114	1-1/4"	100'	19	1.63"	1.66"	1.38"	1.41"	.25"
HF2112	1-1/2"	50'	22	1.865"	1.90"	1.575"	1.60"	.30"
HF22	2"	50'	60	2.34"	2.375"	2.02"	2.045"	.33"

LIQUIDTIGHT FITTINGS

FLEXIBLE LIQUIDTIGHT CONDUIT METALLIC - COIL



6101

FEATURES

- · Crush and corrosion resistant steel core for lasting mechanical protection
- EF PVC jacket is oil and sunlight resistant
- · Smooth interior for easy wire pull through

APPLICATIONS

- For use in damp or wet locations, suitable for commercial and industrial use
- Non UL

STANDARD MATERIAL

• EF PVC jacketed steel core coil wrapped in clear plastic shrink wrap

PART #	SIZE	FEET Coil	MASTER QTY.	WEIGHT/ CASE (LBS.)	INSIDE DIAMETER MIN. MAX.		OUTSIDE Min.	Diameter Max.
6100	3/8"	100'	100'	16	.484"	.504"	.689"	.709"
6101	1/2"	100'	100'	26	.622"	.642"	.819"	.839"
6102	3/4"	100'	100'	31	.815"	.835"	1.032"	1.051"
6103	1"	100'	100'	44	1.032"	1.055"	1.287"	1.315"
6104	1-1/4"	50'	50'	46	1.37"	1.394"	1.63"	1.661"
6105	1-1/2"	50'	50'	35	1.579"	1.598"	1.866"	1.902"
6106	2"	25'	25'	22	2.02"	2.043"	2.339"	2.374"
6106C50	2"	50'	50'	49	2.02"	2.043"	2.339"	2.374"
6107	2-1/2"	25'	25'	42	2.48"	2.504"	2.839"	2.874"
6108	3"	25'	25'	53	3.071"	3.102"	3.461"	3.50"
6109	3-1/2"	25'	25'	55	3.50"	3.54"	3.96"	4"
6110	4"	25'	25'	57	4"	4.039"	4.457"	4.50"

METALLIC - REEL



6101R

FEATURES

- Crush and corrosion resistant steel core for lasting mechanical protection
- EF PVC jacket is oil and sunlight resistant
- Smooth interior for easy wire pull through

APPLICATIONS

- For use in damp or wet locations, suitable for commercial and industrial use
- Non UL

STANDARD MATERIAL

• EF PVC jacketed steel core coil on reel

PART #	SIZE	FEET REEL	MASTER QTY.	WEIGHT/ CASE (LBS.)	INSIDE Min.	DIAMETER MAX.	OUTSIDE I Min.	DIAMETER MAX.
6100R	3/8"	1000'	1000'	182	.484"	.504"	.689"	.709"
6101R	1/2"	1000'	1000'	296	.622"	.642"	.819"	.839"
6102R	3/4"	500'	500'	148	.815"	.835"	1.032"	1.051"
6103R	1"	200'	200'	96	1.032"	1.055"	1.287"	1.315"
6104R	1-1/4"	200'	200'	192	1.37"	1.394"	1.63"	1.661"
6105R	1-1/2"	100'	100'	79	1.579"	1.598"	1.866"	1.902"
6105R150	1-1/2"	150'	150'	120	1.579"	1.598"	1.866"	1.902"
6106R	2"	100'	100'	96	2.02"	2.043"	2.339"	2.374"

FLEXIBLE LIQUIDTIGHT CONDUIT METALLIC - COIL



6100UL



FEATURES

- · Crush and corrosion resistant steel
- core for lasting mechanical protection
- Durable PVC jacket is oil, heat and sunlight resistant(UV)
- Smooth interior for easy wire pull through
- 3/8" thru 1-1/4" with continuous bonding strip

APPLICATIONS

- For use in damp or wet locations,
- suitable for commercial and industrial use
- Listed for direct burial and in poured concrete

STANDARD MATERIAL

- PVC jacketed steel core coil
- wrapped in clear plastic shrink wrap

CERTIFICATIONS

• cULus

PART #	SIZE	FEET Coil	SHIP Case	WEIGHT/ CASE (LBS.)	INSIDE D Min.	iameter Max.	OUTSIDE Min.	Diameter Max.		AMETER PVC Cket Max.
6100UL	3/8"	100'	100'	25	.484"	.504"	.594"	.614"	.690"	.710"
6101UL	1/2"	100'	100'	29	.622"	.642"	.732"	.765"	.820"	.840"
6102UL	3/4"	100'	100'	41	.82"	.84"	.930"	.96"	1.03"	1.05"
6103UL	1"	100'	100'	55	1.04"	1.066"	1.201"	1.226"	1.29"	1.315"
6104UL	1-1/4"	50'	50'	33	1.38"	1.41"	1.54"	1.57"	1.63"	1.66"
6105UL	1-1/2"	50'	50'	54	1.575"	1.60"	1.735"	1.77"	1.865"	1.90"
6106UL	2"	25'	25'	32	2.02"	2.045"	2.18"	2.215"	2.34"	2.375"
6107UL	2-1/2"	25'	25'	46	2.48"	2.505"	2.64"	2.675"	2.84"	2.875"
6108UL	3"	25'	25'	56	3.07"	3.10"	3.295"	3.335"	3.46"	3.50"
6109UL	3-1/2"	25'	25'	69	3.50"	3.54"	3.72"	3.789"	3.96"	4"
6110UL	4"	25'	25'	80	4"	4.22"	4.22"	4.28"	4.46"	4.50"

METALLIC - REEL



FEATURES

- Crush and corrosion resistant steel
- core for lasting mechanical protection • Durable PVC jacket is oil, heat and sunlight resistant(UV)
- Smooth interior for easy wire pull through
- 3/8" thru 1-1/4" with continuous bonding strip

APPLICATIONS

- For use in damp or wet locations,
- suitable for commercial and industrial use • Listed for direct burial and in poured concrete

STANDARD MATERIAL

• PVC jacketed steel core coil on reel CERTIFICATIONS

cULus

PART #	SIZE	FEET REEL	SHIP Case	WEIGHT/ Case (LBS.)	INSIDE DI Min.	AMETER MAX.	OUTSIDE E Min.	DIAMETER MAX.	OUTSIDE DIA Jac Min.	AMETER PVC Ket Max.
6100RUL	3/8"	1000'	1000'	272	.484"	.504"	.594"	.614"	.69"	.71"
6101RUL	1/2"	1000'	1000'	312	.622"	.642"	.732"	.765"	.82"	.84"
6101RUL500	1/2"	500'	500'	156	.622"	.642"	.732"	.765"	.82"	.84"
6102RUL	3/4"	500'	500'	229	.82"	.84"	.93"	.96"	1.03"	1.05"
6103RUL	1"	200'	200'	127	1.04"	1.066"	1.201"	1.226"	1.29"	1.315"
6104RUL	1-1/4"	200'	200'	155	1.38"	1.41"	1.54"	1.57"	1.63"	1.66"
6105RUL	1-1/2"	100'	100'	130	1.575"	1.60"	1.735"	1.77"	1.865"	1.90"
6106RUL	2"	100'	100'	154	2.02"	2.045"	2.18"	2.215"	2.34"	2.375"

US



Southwire[™] LIQUIDTIGHT CATALOG

get social with us:



/SOUTHWIRETOOLS



/SOUTHWIRE-COMPANY







WWW.SOUTHWIRE.COM | 1-855-SWTOOLS

All Trademarks or Registered Trademarks (TM/®) are owned or licensed by Southwire Company Any other ™/®- Trademark or Registered Trademark of Southwire Company.

SCAN TO LEARN MORE